

**M8 male 90° / M12 female 0° A-cod.**

PVC 4x0.25 gy UL/CSA 0.6m

Art.No.: 7000-88311-2110060

Weight: 0.036 kg

Country of origin: CZ

Model designation: MSBL0-I-T211\_0.6

**Advantages of our connectors:**

Our connectors are versatile and specially optimised for industrial environments. All connectors are 100% tested during the manufacturing process to ensure the highest quality and reliability.

The contacts are gold-plated, which ensures optimum conductivity. Thanks to the high degree of protection, the connectors are ideal for demanding industrial environments. They are also vibration-resistant - this is ensured by the union nut with vibration protection.

Our connectors are resistant to oils and cooling lubricants, but resistance to aggressive media should be tested for each specific application. Different cable lengths available [on request](#)

If you are missing technical information? Please feel free to use our [dictionary](#) to find more technical details.

**Product details:**

Male 90° – female straight

M8 – M12, 4-pole


A-coded






Art-No. 7005 - M12/M8 Lite - (plastic hexagonal screw) on request


Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[\*\*Link to Product\*\*](#)
**Illustration**






Product may differ from Image



#### Header

Material short text	MSBL0-I-T211_0.6
---------------------	------------------

Cable length	0,60 m
--------------	--------

#### Side 1

Family construction form	M8
--------------------------	----

No. of poles	4
--------------	---

Coding	A
--------	---

Mounting method	inserted, screwed
-----------------	-------------------

Threaded hole	M8 x 1
---------------	--------

Tightening torque	0,4 Nm
-------------------	--------

Width across flats	SW9
--------------------	-----

suitable for corrugated tube (internal Ø)	6,5 mm
---	--------

Material contact	Copper alloy
------------------	--------------

Coating contact	gold plated
-----------------	-------------

#### Side 2

Family construction form	M12
--------------------------	-----

No. of poles	4
--------------	---

Coding	A
--------	---

Mounting method	inserted, screwed
-----------------	-------------------

Threaded hole	M12 x 1
---------------	---------

Tightening torque	0,6 Nm
-------------------	--------

Width across flats	SW13
--------------------	------

suitable for corrugated tube (internal Ø)	10 mm
---	-------

Material contact	Copper alloy
------------------	--------------

Coating contact	gold plated
-----------------	-------------

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/7000-88311-2110060">https://shop.murrelektronik.com/7000-88311-2110060</a>
-------------	---

GTIN	4048879121217
------	---------------

ECLASS-6.0	27279218
------------	----------

ECLASS-6.1	27279218
------------	----------

ECLASS-7.0	27279218
------------	----------

ECLASS-7.1	27279218
------------	----------

ECLASS-8.0	27279218
------------	----------

ECCLASS-8.1	27279218
ECCLASS-9.0	27060311
ECCLASS-9.1	27060311
ECCLASS-10.0.1	27060311
ECCLASS-10.1	27060311
ECCLASS-11.0	27060311
ECCLASS-11.1	27060311
ECCLASS-12.0	27060311
ECCLASS-13.0	27060311
ECCLASS-14.0	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444290
EAN	4048879121217
Packaging unit	1

#### Electrical data | Supply

Operating voltage AC	50 V
Operating voltage DC	60 V
Current operating per contact max.	4 A

#### Diagnostics

Status indication LED	No
-----------------------	----

#### Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67, IP68, IP66K, IP65
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	1,5 kV
Material group (IEC 60664-1)	I

#### Mechanical data | Material data

Material housing	PUR
Locking material	Zinc die-casting
Coating locking	Nickelated
Material gasket	FKM

#### Mechanical data | Mounting data

Mounting method	inserted, screwed, Shaking protection
-----------------	---------------------------------------

#### Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

#### Important installation notes

Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

#### Installation | Cable

Cable identification	211
Cable Type	1
Amount stranding	1
Stranding	4 wires stranded
Wire arrangement	brown, black, blue, white
Cable weight	31,6 g/m

Material wire insulation	PVC
Amount wires	4
Outer diameter insulation	1,25 mm
Outer diameter tolerance core insulation	± 0,05 mm
Shore hardness wire insulation	45 ± 5 Shore D
Material properties wire insulation	good machinability
Ingredient freeness wire insulation	lead-free, cadmium-free, CFC-free, silicone-free
Amount strands (wire)	14
Diameter of single wires	0,15 mm
Conductor crosssection (wire)	0,25 mm <sup>2</sup>
Material conductor wire	Stranded copper wire, bare
Conductor type (wire)	Strand class 5
Outer-diameter (jacket)	4,8 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	PVC
Shore hardness jacket	85 ± 5 Shore A
Freedom from ingredients (jacket)	lead-free, cadmium-free, CFC-free, silicone-free
Material property (jacket)	good machinability
Conductor resistance (wire)	79 Ω/km @ 20 °C
Nominal voltage max.	300 V
Withstand voltage (wire - wire)	2 kV @ 60 s
Withstand voltage (wire - jacket)	2 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity max. (wire)	3,6 A
Operating temperature min. (static)	-30 °C
Operating temperature max. (static)	80 °C
Operating temperature min. (dynamic)	-5 °C
Operating temperature max. (dynamic)	80 °C
Flame resistance	UL 1581 § 1080, CSA FT1, IEC 60332-1-2
Oil resistance	good
Chemical resistance	good
Other resistances	good resistance to gasoline
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter