

M12-PANEL FEED THROUGH 5POLE B CODED, V2A

Art.No.: 7002-44111-0000000

Weight: 0.027 kg

Country of origin: CZ

Model designation: MSBBSV-BA-U-S02

Control cabinet entry system




Male - female


M12, 5-pole

B-coded

Shielded

Stainless steel 1.4305 (V2A)

[Link to Product](#)**Illustration**



Product may differ from Image

Side 1

Family construction form M12

Commercial data

URL Webshop	https://shop.murrelektronik.com/7002-44111-0000000
GTIN	4048879483728
EU-Customs tariff number	85366990
US-Customs tariff number	8536694020
ECLASS-6.0	27279221
ECLASS-6.1	27279220
ECLASS-7.0	27440103
ECLASS-7.1	27440103
ECLASS-8.0	27440103
ECLASS-8.1	27440103
ECLASS-9.0	27440109
ECLASS-9.1	27440109
ECLASS-10.0.1	27440109
ECLASS-10.1	27440109
ECLASS-11.0	27440109
ECLASS-11.1	27440109
ECLASS-12.0	27440109
ECLASS-13.0	27440109
ECLASS-14.0	27440109
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85366990
EAN	4048879483728
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	60 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A

Installation | Connection

Tightening torque	0,6 Nm
Mounting set	M16 x 1.5

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Mechanical data Material data	
housing	Stainless steel 1.4305 (V2A)
Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.