

MDC06-4s / MDC06-4s

PUR / PVC 2x1.5+1x2x0.5 sw 2.5m

Art.No.: 7072-77095-2600250

Weight: 0.326 kg

Country of origin: DE

Model designation: MSTD4L0-TD4-T260_2.5-S72

Xtreme - Outdoor

Male straight – male straight

6 ... 32 V AC/DC

4-pole

without components





Compatible with:


Deutsch DT06-4S

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**



Product may differ from Image



Cable length	2,50 m
Side 1	
Family construction form	MDC
No. of poles	4
Mounting method	inserted
suitable for corrugated tube (internal Ø)	13 mm
Material contact	Copper alloy
Coating contact	nickel plated
Side 2	
Family construction form	MDC
No. of poles	4
Mounting method	inserted
suitable for corrugated tube (internal Ø)	13 mm
Coating contact	nickel plated
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7072-77095-2600250
GTIN	4065909007853
Customs tariff number	85444290
ECLASS-6.0	27279218
ECLASS-6.1	27279218
ECLASS-7.0	27279218
ECLASS-7.1	27279218
ECLASS-8.0	27279218
ECLASS-8.1	27279218
ECLASS-9.0	27060312
ECLASS-9.1	27060312
ECLASS-10.0.1	27060312
ECLASS-10.1	27060312
ECLASS-11.0	27060312
ECLASS-11.1	27060312
ECLASS-12.0	27060312
ECLASS-13.0	27060312
ECLASS-14.0	27060312

ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444290
EAN	4065909007853
Packaging unit	1

Electrical data | Supply

Operating voltage AC min.	6 V
Operating voltage AC max.	32 V
Operating voltage DC min.	6 V
Operating voltage DC max.	32 V
Current operating per contact max.	4 A

Diagnostics

Status indication LED	No
-----------------------	----

Installation | Connection

Family construction form	Amphenol AT06-4S
--------------------------	------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP69K, IP68, IP66K
Additional condition protection degree	inserted
Pollution Degree	2
Additional suppressor	without components
Rated surge voltage	0,8 kV
Material group (IEC 60664-1)	III

Mechanical data | Material data

housing	PA
Gasket	Silicon

Mechanical data | Mounting data

Looking techniques	Snap-in connector
--------------------	-------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Installation | Cable

Stranding	1 × 2 wires stranded
Stranding (type 2)	1 × 2 wires stranded with filler with stranding combination
Filler	Yes
Wire arrangement	(OG, GN), BN, BU
Material wire insulation	PVC
Amount wires	2
Outer diameter insulation	2.25 mm ± 0.1 mm
Conductor crosssection (wire)	1,5 mm ²
Material conductor wire	Stranded copper wire, bare
Core construction (wire)	84 × 0.15 mm
Ingredient freeness wire insulation	lead-free, CFC-free
Material wire insulation (type 2)	PP
Amount wires (type 2)	2

Outer diameter wire insulation (type 2)	2 mm ± 0.1 mm
Conductor crosssection (wire type 2)	0,5 mm ²
Material conductor wire (type 2)	Stranded copper wire, bare
Core construction (wire type 2)	16 × 0.2 mm
Ingredient freeness wire insulation (type 2)	lead-free, CFC-free, halogen-free
Material jacket	PUR
Outer-diameter (jacket)	8.8 mm ± 5 %
Jacket Color	black / RAL 9005
Material inner jacket	PVC
Color (inner jacket)	black
Freedom from ingredients (jacket)	lead-free, cadmium-free, CFC-free
Material property (jacket)	abrasion-resistant, low adhesion, good machinability, matte
Conductor resistance (wire)	13.3 Ω/km @ 20 °C
Conductor resistance (wire type 2)	40.1 Ω/km @ 20 °C
Nominal voltage max.	60 V
Withstand voltage (wire - wire)	1 kV @ 60 s
Withstand voltage (wire - jacket)	1 kV @ 60 s
Current load capacity max. (wire)	14,4 A
Current load capacity max. Wire (type 2)	7,2 A
Current load capacity (standard)	to DIN VDE 0298-4
Isolation resistance	20 MΩ × km
Cable type	CAN-Bus
Operating temperature (static)	-40 °C ... 85 °C
Operating temperature (dynamic)	-30 °C ... 85 °C
Other resistances	resistant to hydrolysis, resistant to microbes
Notes	application-related testing
Bending radius (fixed)	6 × Outer diameter
Bending radius (dynamic)	12 × Outer diameter