

**Cable drum Ø 355mm**

PUR 4x0.34 ye UL/CSA+drag ch. 100m

Art.No.: 7000-C0101-0340000

Weight: 5.133 kg

Country of origin: DE

Model designation: 100m Kabel 10080637(034)auf Spule 01


Cable drum (100 m)

PUR (UL/CSA)

4× 0.34 mm<sup>2</sup>, yellow

suitable for C-tracks

5 Mio.

**[Link to Product](#)****Illustration**

Product may differ from Image

**Header**

Material short text

100m Kabel 10080637(034)auf Spule 01

**Commercial data**

The information in this Product-PDF has been compiled with the utmost care.  
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-02-09

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

|                       |                                                                                                                     |
|-----------------------|---------------------------------------------------------------------------------------------------------------------|
| URL Webshop           | <a href="https://shop.murrelektronik.com/7000-C0101-0340000">https://shop.murrelektronik.com/7000-C0101-0340000</a> |
| GTIN                  | 4048879313841                                                                                                       |
| ECLASS-6.0            | 27062011                                                                                                            |
| ECLASS-6.1            | 27061801                                                                                                            |
| ECLASS-7.0            | 27061801                                                                                                            |
| ECLASS-7.1            | 27061801                                                                                                            |
| ECLASS-8.0            | 27061801                                                                                                            |
| ECLASS-8.1            | 27061801                                                                                                            |
| ECLASS-9.0            | 27061801                                                                                                            |
| ECLASS-9.1            | 27061801                                                                                                            |
| ECLASS-10.0.1         | 27061801                                                                                                            |
| ECLASS-10.1           | 27061801                                                                                                            |
| ECLASS-11.0           | 27061801                                                                                                            |
| ECLASS-11.1           | 27061801                                                                                                            |
| ECLASS-12.0           | 27061801                                                                                                            |
| ECLASS-13.0           | 27061801                                                                                                            |
| ECLASS-14.0           | 27061801                                                                                                            |
| ETIM-5.0              | EC001855                                                                                                            |
| ETIM-6.0              | EC001855                                                                                                            |
| ETIM-7.0              | EC001855                                                                                                            |
| ETIM-8.0              | EC001855                                                                                                            |
| customs tariff number | 85444995                                                                                                            |
| EAN                   | 4048879313841                                                                                                       |
| Packaging unit        | 1                                                                                                                   |

#### Important installation notes

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |

#### Installation | Cable

|                                          |                                                                |
|------------------------------------------|----------------------------------------------------------------|
| Cable identification                     | 034                                                            |
| Cable Type                               | 3                                                              |
| Stranding                                | 1 × 4 wires stranded                                           |
| Wire arrangement                         | brown, black, blue, white                                      |
| Cable weight                             | 33 g/m                                                         |
| Material wire insulation                 | PP                                                             |
| Amount wires                             | 4                                                              |
| Outer diameter insulation                | 1,25 mm                                                        |
| Outer diameter tolerance core insulation | ± 0,05 mm                                                      |
| Shore hardness wire insulation           | 70 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation      | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                    | 42                                                             |
| Diameter of single wires                 | 0,1 mm                                                         |
| Conductor crosssection (wire)            | 0,34 mm²                                                       |
| Material conductor wire                  | Stranded copper wire, bare                                     |
| Conductor type (wire)                    | strand class 6                                                 |
| Outer-diameter (jacket)                  | 4,5 mm                                                         |
| Tolerance outer diameter (sheath)        | ± 5 %                                                          |
| Material jacket                          | PUR                                                            |
| Shore hardness jacket                    | 90 ± 5 Shore A                                                 |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Material property (jacket)               | abrasion-resistant, low adhesion, good machinability, matte    |
| Conductor resistance (wire)              | 57 Ω/km @ 20 °C                                                |
| Nominal voltage max.                     | 300 V                                                          |
| Withstand voltage (wire - wire)          | 2.5 kV @ 60 s                                                  |

|                                         |                                                                             |
|-----------------------------------------|-----------------------------------------------------------------------------|
| Withstand voltage (wire - jacket)       | 2.5 kV @ 60 s                                                               |
| Current load capacity (standard)        | to DIN VDE 0298-4                                                           |
| Current load capacity max. (wire)       | 4,8 A                                                                       |
| Operating temperature min. (static)     | -40 °C                                                                      |
| Operating temperature max. (static)     | 80 °C / 90 °C @ 10000 h Operation                                           |
| Operating temperature min. (dynamic)    | -25 °C                                                                      |
| Operating temperature max. (dynamic)    | 80 °C / 90 °C @ 10000 h Operation                                           |
| Operating temperature min. (drag chain) | -25 °C                                                                      |
| Operating temperature max. (drag chain) | 80 °C / 90 °C @ 10000 h Operation                                           |
| Flame resistance                        | UL 1581 § 1090, CSA FT2, IEC 60332-2-2                                      |
| Oil resistance                          | IEC 60811-404                                                               |
| Chemical resistance                     | good                                                                        |
| Other resistances                       | good resistance to gasoline, resistant to hydrolysis, resistant to microbes |
| Bending radius (fixed)                  | 5 × Outer diameter                                                          |
| Bending radius (dynamic)                | 10 × Outer diameter                                                         |
| No. of bending cycles (C-track)         | 10 Mio. @ 25 °C                                                             |
| Traversing distance (C-track)           | 10 m @ 25 °C   horizontal                                                   |
| Travel speed (C-track)                  | 3 m/s @ 25 °C                                                               |
| Acceleration (C-track)                  | 10 m/s² @ 25 °C                                                             |
| No. of torsion cycles                   | 5 Mio.                                                                      |
| Torsion stress                          | ± 360 °/m                                                                   |
| Torsion speed                           | 35 cycles/min                                                               |