

Cable drum Ø 500mm

PUR AWG24+22 shielded vt UL/CSA+drag ch. 200m

Art.No.: 7000-C0502-8030000

Weight: 14.484 kg

Country of origin: IT

Model designation: 200m Kabel 50080919(803)auf Kabeltr

Cable drum (200 m)


DeviceNet, CANopen

2× 0.25 + 2× 0.34 mm²

PUR (UL/CSA)

suitable for C-tracks

5 Mio.

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

200m Kabel 50080919(803)auf Kabeltr

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-C0502-8030000
GTIN	4048879430739
ECLASS-6.0	27062011
ECLASS-6.1	27061801
ECLASS-7.0	27061801
ECLASS-7.1	27061801
ECLASS-8.0	27061801
ECLASS-8.1	27061801
ECLASS-9.0	27061801
ECLASS-9.1	27061801
ECLASS-10.0.1	27061801
ECLASS-10.1	27061801
ECLASS-11.0	27061801
ECLASS-11.1	27061801
ECLASS-12.0	27061801
ECLASS-13.0	27061801
ECLASS-14.0	27061801
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444995
EAN	4048879430739
Packaging unit	1

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Installation | Cable

Cable identification	803
Function cable	Hybrid, Data, Power
Stranding	2 × 2 wires stranded
Amount stranding (type 2)	1
Stranding (type 2)	1 × 2 stranding combinations stranded
Cable shielding (type)	copper braid, tinned
Cable shielding (coverage)	65 %
Banding	Foil
Drain wire (cross-section)	22 AWG
Wire arrangement	(white, blue), (black, red)
Cable weight	57,38 g/m
Material wire insulation	PE
Amount wires	2
Outer diameter insulation	2,1 mm
Outer diameter tolerance core insulation	± 0,05 mm
Shore hardness wire insulation	65 ± 5 Shore D
Ingredient freeness wire insulation	lead-free, CFC-free, halogen-free
Amount strands (wire)	19
Diameter of single wires	36 AWG
Conductor crosssection (wire)	24 AWG
Drain wire (cross-section)	22 AWG
Material conductor wire	copper stranded wire, tinned
Electrical function wire	Data

Material wire insulation (type 2)	PE
Outer diameter wire insulation (type 2)	1,5 mm
Tolerance outer diameter wire insulation (type 2)	± 0,05 mm
Shore hardness wire insulation (type 2)	65 ± 5 Shore D
Ingredient freeness wire insulation (type 2)	lead-free, CFC-free, halogen-free
Amount wires (type 2)	2
Amount strands wire (type 2)	19
Diameter of single wires (type 2)	34 AWG
Conductor crosssection wire (type 2)	22 AWG
Material conductor wire (type 2)	copper stranded wire, tinned
Electrical function wire (type 2)	Power
Outer-diameter (jacket)	6,9 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	PUR
Shore hardness jacket	89 ± 5 Shore A
Freedom from ingredients (jacket)	lead-free, CFC-free, halogen-free
Conductor resistance (wire)	94.2 Ω/km @ 20 °C
Conductor resistance (wire type 2)	59.4 Ω/km @ 20 °C
Electric capacitance	40.000 pF/km
Isolation resistance	5.000 MΩ × km
Nominal voltage max.	300 V
Withstand voltage (wire - wire)	2 kV @ 60 s
Withstand voltage (wire - shield)	2 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity max. (wire)	3 A
Current load capacity max. Wire (type 2)	6 A
Characteristic impedance	120 Ω ± 10 % @ 10 MHz
Operating temperature min. (static)	-40 °C
Operating temperature max. (static)	80 °C
Operating temperature min. (dynamic)	-30 °C
Operating temperature max. (dynamic)	70 °C
Flame resistance	IEC 60332-1-2, UL 1581 § 1060, UL 1581 § 1090, UL 1581 § 1100
Oil resistance	IEC 60811-404, IRM 901
Ozone resistance	IEC 60811-403, EN 50396
UV resistance	UL 1581 § 1200 @ 300 h
Other resistances	good resistance to saturated hydrocarbons (diesel, kerosene, petrol ether), resistant to microbes, MUD-resistant (NEK 606)
Bending radius (fixed)	6 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter
No. of bending cycles (C-track)	1 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C
Travel speed (C-track)	3 m/s @ 25 °C
Acceleration (C-track)	5 m/s² @ 25 °C