Description

- The standard for housings. Large selection of different inserts.
- Easy-to-grip, user-friendly design makes it easy to plug and unplug the connector.





General Characteristics

Series	H-B 10
Locking	double lever
Cable entry	top / side
Protection (DIN EN 60529)	IP 65 (latched)
Protection (NEMA 250, UL50E)	4, 12 (latched)
Temperature Range	-40°C to +125°C

Materials and Surfaces

Housing	aluminium alloy, powder-coated, grey
Lever	steel, zinc-plated

Approvals

UL-Approval, E-File-Number	E75770

Standard

Safety Standard	IEC 61984


Versions


Article number	Article description	Thread M	Cable entry
19041000	EPIC® H-B 10 TGB M20	M20x1,5	top
79055700	EPIC® H-B 10 TGB M25	M25x1,5	top
19045000	EPIC® H-B 10 TSB M20	M20x1,5	side
79057700	EPIC® H-B 10 TSB M25	M25x1,5	side

We reserve all rights according to DIN ISO 16016.


Technical Drawings

Top cable entry





Side cable entry



Industrial machinery and plant engineering

Mechanical resistance

Robust

Waterproof

Automation

Info

Universal, robust metal housings size H-B 10

Application range

Plant engineering, Light & sound technology, Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

We reserve all rights according to DIN ISO 16016.