

22262040	DATA SHEET	
Valid from: 17.06.2024	AB-C4-M12MS-(L*)TPE-HD	

Product description

- Sensor / actuator cable, 4-pol, PP-EPDM
- Straight M12-plug on free conductor end
- Hygienic Design for Food & Beverage



General characteristics

Number of pins	4
Ambient temperature	-40 °C to +105 °C (-40°F to 221°F) (plug / jack) -40 °C to +105 °C (-40°F to 221°F) (cable, fixed installation) -25 °C to +105 °C (-13°F to 221°F) (cable, movable installation)
Degree of protection	IP65 / IP67 / IP68 / IP69
Coding	A-standard
Plugging cycles	≥ 100
Tightening torque	0,4 Nm (M12-connector)

Variation

Article number	Description	Length [m]	Configuration
22262040	AB-C4-M12MS-2,0TPE-HD	2	straight
22262041	AB-C4-M12MS-5,0TPE-HD	5	straight
22262060	AB-C4-M12MS-7,5TPE-HD	7,5	straight
22262042	AB-C4-M12MS-10,0TPE-HD	10	straight
22262061	AB-C4-M12MS-15,0TPE-HD	15	straight

Additional note

Data sheet also valid for variant lengths. Other lengths on request.

Electrical properties

Rated voltage	250 V
Rated current	4 A
Overvoltage category	II
Pollution degree	3

Mechanical properties

Plug

Contact, material	CuSn
Contact carrier, material	PP
Contact surface, material	Ni/Au
Knurl, material	Stainless steel
Handle, material	PP

Line

Cable construction	4 x AWG22/42
Signal line, construction	42 x 0,1 mm
Conductor cross-section	0,34 mm ²
Conductor diameter including isolation	1,27 mm ± 0,02 mm

Creator: THLE3/PDP Released: FELI1/PDP	Document: DB22262040EN Version: 01	Page 1 of 2
---	---------------------------------------	-------------

22262040	DATA SHEET	
Valid from: 17.06.2024	AB-C4-M12MS-(L*)TPE-HD	




Cable outer diameter D	4,7 mm ± 0,15 mm
Insulation color	Brown, white, blue, black
Sheath color	grey, RAL 7035
Number of bending cycles	4.000.000
Minimum bending radius	10 x D
Traveling distance	10 m
Traveling speed	3 m/s
Acceleration	10 m/s ²
Cable weight	30 kg/km
Outer coating, material	PP-EPDM
Wire insulation, material	PP
Insulation resistance	≥ 1 GΩ*km
Conductor resistance	approx. 58 MΩ/km
Halogen-free	acc. to DIN VDE 0472 Part 815
Other characteristics	Resistant to cold wraps and cold shock according to DIN EN 60811-1-4 (-40 °C)

Standards/Approvals


Product standard, M12 connector
Material compliance

IEC 61076-2-101
FDA 21 CFR 177.2600

Technical drawing



Wire cross section



Application range

For food and packaging machines.

Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: THLE3/PDP Released: FELI1/PDP	Document: DB22262040EN Version: 01	Page 2 of 2
---	---------------------------------------	-------------