

EPIC® DATA PB TR M12

M12 Terminating resistor for PROFIBUS

Extremely robust M12 bus termination (resistor) for individuell use within field bus networks (PROFIBUS, DeviceNet and CANopen).

Info

Fully suitable for industrial use



Supplementary automation components from Lapp



Assembly time



Space requirement

Benefits

Cost efficient termination of a bus systems

Space-saving due to compact dimensions.

Robust design

Application range

Mechanical and plant engineering

Product features

150 Ω terminating resistor for PROFIBUS

Product Make-up

Straight connector M12 with integrated termination resistor

Straight connector M12, with integrated termination resistor, shielded

Technical Data

Last Update (19.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® DATA PB TR M12

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000448 ETIM 5.0 Class-Description: Terminal resistor
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000448 ETIM 6.0 Class-Description: Terminal resistor
Protection rating:	IP65/IP67 (plug) IP 67 (socket)
Ambient temperature (operation):	-25°C to +90°C (plug) -40°C to +85°C (socket)
Contact material:	CuSn
Coding:	B - inverse (PROFIBUS)
Rated current (A):	4 A

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® DATA PB TR M12

Article number	Article designation	Number of pins	Rated voltage (V)	PU
Plug, unshielded (terminating resistor)				
22260722	AB-C4-M12MS-PB-TR	4	60	5
Socket, shielded (terminating resistor)				
22261001	AB-C5-M12FS-PB-TR-SH	4	32	1

Last Update (19.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16