

Q25 AC Voltage Series Sensor Quick Start Guide



Features

Self-contained, AC-operated sensors

For complete technical information about this product, including installation instructions, application requirements and guidelines, technical specifications, and accessories, go to www.bannerengineering.com and search 121517.



WARNING:

- **Do not use this device for personnel protection**
- Using this device for personnel protection could result in serious injury or death.
- This device does not include the self-checking redundant circuitry necessary to allow its use in personnel safety applications. A device failure or malfunction can cause either an energized (on) or de-energized (off) output condition.

Models

Opposed mode sensors

Model	Output	Range	Connector
Q253E	N/A	20 m (65.6 ft)	2 m (6.5 ft) cable
Q253EQ1	N/A		4-pin 1/2 in-20UNF (1/2-in Dual Key) male quick disconnect (QD)
Q25AW3R	LO		2 m (6.5 ft) cable
Q25RW3R	DO		2 m (6.5 ft) cable

Polarized retroreflective mode sensors

Model	Output	Range	Connector
Q25AW3LP	LO	2 m (6.6 ft)	2 m (6.5 ft) cable
Q25AW3LPQ1	LO		4-pin 1/2 in-20UNF (1/2-in Dual Key) male quick disconnect (QD)
Q25RW3LP	DO		2 m (6.5 ft) cable
Q25RW3LPQ1	DO		4-pin 1/2 in-20UNF (1/2-in Dual Key) male quick disconnect (QD)

Fixed-field mode sensors

Model	Output	Range	Connector
Q25AW3FF25Q1	LO	25 mm (0.9 in) cutoff	4-pin 1/2 in-20UNF (1/2-in Dual Key) male quick disconnect (QD)
Q25AW3FF50	LO	50 mm (1.9 in) cutoff	2 m (6.5 ft) cable
Q25AW3FF50Q1	LO		4-pin 1/2 in-20UNF (1/2-in Dual Key) male quick disconnect (QD)
Q25AW3FF100Q1	LO	100 mm (3.9 in) cutoff	4-pin 1/2 in-20UNF (1/2-in Dual Key) male quick disconnect (QD)
Q25RW3FF100	DO		2 m (6.5 ft) cable
Q25RW3FF100Q1	DO		4-pin 1/2 in-20UNF (1/2-in Dual Key) male quick disconnect (QD)



A model with a QD connector requires a mating cable.

In light operate (LO) mode, the output is ON when the target returns the same or more light to the sensor and OFF when the sensor detects less light than the configured/taught target. In **opposed and retroreflective sensing modes**, light operate is active when the beam is unblocked. In **diffuse, fixed field, and adjustable field sensor modes**, light operate is active when the target is present.


In dark operate (DO) mode, the output is ON when the target returns less light to the sensor than the configured target and OFF when the sensor detects more light than the configured/taught target. In **opposed and retroreflective sensing modes**, dark operate is active when the beam is blocked. In **diffuse, fixed field, and adjustable field sensor modes**, dark operate is active when the target is absent.




Wiring Diagrams




4-pin 1/2 in-20UNF (1/2-in Dual Key) quick disconnect emitters



All other 4-pin 1/2 in-20UNF (1/2-in Dual Key) quick disconnect models



4-pin 1/2 in-20UNF (1/2-in Dual Key) male pinout



Key:

- 1 - Red/black
- 2 - Red/white
- 3 - Red
- 4 - Green

Specifications

Supply Voltage and Current

20 V to 250 V AC (50 Hz/60 Hz)
Average current: 20 mA
Peak current:
200 mA at 20 V AC
500 mA at 120 V AC
750 mA at 250 V AC

Sensing LED Beam

Opposed mode: Infrared, 950 nm
Polarized retroreflective mode: Visible red, 680 nm
Fixed-field mode: Infrared, 880 nm

Supply Protection Circuitry

Protected against transient voltages

Output Configuration

SPST solid-state AC switch; three-wire connection; light operate or dark operate, depending on model
Light Operate: Output conducts when the sensor sees its own (or the emitter's) modulated light
Dark Operate: Output conducts when the sensor sees dark

Output Response

Time Opposed mode: 16 ms ON, 8 ms OFF
Other models: 16 ms ON and OFF

NOTE: 100 ms delay on power-up; outputs do not conduct during this time

Output Rating

300 mA maximum (continuous)
Fixed-Field models: derate 5 mA/°C above +50° C (+122° F)
Inrush capability: 1 amp for 20 ms, non-repetitive
OFF-state leakage current: < 100 µA
ON-state saturation voltage: 3 V at 300 mA AC; 2 V at 15 mA AC

Output Protection Circuitry

Protected against false pulse on power-up

Repeatability

Opposed mode: 2 ms
Other models: 4 ms
Repeatability and response are independent of signal strength

Indicators

Two LEDs (Green and Amber)
Green ON steady: Power to the sensor is ON
Amber ON steady: The sensor sees light
Amber flashing: Excess gain marginal (1 to 1.5 times) in light condition

Construction

PBT polyester housing; polycarbonate (opposed-mode) or acrylic lens

Environmental Rating

Leakproof design rated NEMA 6P, DIN 40050 (IP69K per ISO 20653)

Connections

2 m (6.5 ft) attached cable or 4-pin 1/2 in-20UNF (1/2-in Dual Key) quick-disconnect fitting, depending on the model ordered

Operating Conditions

Temperature: -40 °C to +70 °C (-40 °F to +158 °F)
Humidity: 90% at +50 °C maximum relative humidity (non-condensing)

Vibration and Mechanical Shock

All models meet MIL-STD-202F, Method 201A (Vibration: 10 Hz to 60 Hz maximum, 0.06 inch (1.52 mm) double amplitude, 10G acceleration) requirements. Method 213B conditions H&I. (Shock: 75G with device operating; 100G for non-operation)

Certifications



Banner Engineering BV
Park Lane, Culliganlaan 2F bus 3
1831 Diegem, BELGIUM



Turck Banner LTD Blenheim House
Blenheim Court
Wickford, Essex SS11 8YT
GREAT BRITAIN



Required Overcurrent Protection



WARNING: Electrical connections must be made by qualified personnel in accordance with local and national electrical codes and regulations.

Overcurrent protection is required to be provided by end product application per the supplied table.

Overcurrent protection may be provided with external fusing or via Current Limiting, Class 2 Power Supply.

Supply wiring leads < 24 AWG shall not be spliced.

For additional product support, go to www.bannerengineering.com.

Supply Wiring (AWG)	Required Overcurrent Protection (A)	Supply Wiring (AWG)	Required Overcurrent Protection (A)
20	5.0	26	1.0
22	3.0	28	0.8
24	2.0	30	0.5

Banner Engineering Corp Limited Warranty

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEALING OR TRADE USAGE.

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. **IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.**

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp. Any misuse, abuse, or improper application or installation of this product or use of the product for personal protection applications when the product is identified as not intended for such purposes will void the product warranty. Any modifications to this product without prior express approval by Banner Engineering Corp will void the product warranties. All specifications published in this document are subject to change; Banner reserves the right to modify product specifications or update documentation at any time. Specifications and product information in English supersedes that which is provided in any other language. For the most recent version of any documentation, refer to: www.bannerengineering.com.

For patent information, see www.bannerengineering.com/patents.