

## Features

30 mm Multi-Color General-Purpose or Audible Indicators



- Rugged, affordable, and easy-to-install multi-segment indicators
- Compact 30 mm diameter
- Illuminated segments provide easy-to-see operator guidance and indication of equipment status
- Uniform indicator segments appear gray when off to eliminate false indication from ambient light
- Models with 2, 3, 4, and 5 color segments plus audible
- 12 V DC to 30 V DC operation
- No assembly required, mounting nut and gasket supplied

## Models



Housing	Color Position					Audible Alarm	Housing Color	Connection <sup>(1)</sup>
	1	2	3	4	5			
TL30B	G	Y	R	X	X	N	X	QD
	G = Green Y = Yellow R = Red B = Blue W = White X = No segment (applies to color positions 3, 4, and 5 only)					N = None A = Audible	X = Black	C1 = Integral 1.2 m (3.9 ft) PVC-jacketed cable QD = Integral 5-pin or 8-pin M12 male quick disconnect connector

## Wiring

**NOTE:** All models are bimodal and can be wired as PNP or NPN devices.

<sup>(1)</sup> Models with a quick-disconnect connector require a mating cordset.


## 5-Pin/Wire Models




1 = Brown  
2 = White  
3 = Blue  
4 = Black  
5 = Gray  
C1 = Color 1  
C2 = Color 2  
C3 = Color 3  
C4 = Color 4  
A = Audible

Pin 5 (Gray wire) activates the corresponding color or the audible function, if available.  
2 and 3 segment models only require associated wires to be connected.

## 8-Pin / 7-Wire Models



Pinout and Key



1 = White  
2 = Brown  
3 = Green (Not Used)  
4 = Yellow  
5 = Gray  
6 = Pink  
7 = Blue  
8 = Red  
C1 = Color 1  
C2 = Color 2  
C3 = Color 3  
C4 = Color 4  
C5 = Color 5  
A = Audible

Green wire not used.

## Specifications

## Supply Voltage and Current

12 V DC to 30 V DC

Maximum current per LED segment: 40 mA

**Omni-Directional Sealed Audible Alarm:** 20 mA maximum current

## Supply Protection Circuitry

Protected against transient voltages

## Input Leakage Current Immunity

400  $\mu$ A<sup>(2)</sup>

## Audible Alarm

**Omni-Directional Sealed Audible Alarm:** 2.8 kHz  $\pm$  500 Hz oscillation frequency, maximum intensity 90 dB at 1 m (3.3 ft) (typical)

## Operating Conditions

-40 °C to +50 °C (-40 °F to +122 °F)

90% maximum relative humidity (non-condensing)

Storage Temperature: -40 °C to +70 °C (-40 °F to +158 °F)

<sup>(2)</sup> Any current above this value may activate the TL30.

## Environmental Rating

## All Models:

IP65

UL Type 4X when mounted in a UL Type 4X enclosure

**Non-Audible:** UL Type 13 when mounted in a UL Type 13 enclosure

## Indicators

LEDS are independently selected; 2 to 5 colors depending on model

## Indicator Response Time

Indicator On/Off: 1 millisecond maximum

## Indicator Characteristics

Color	Dominant Wavelength (nm) or Color Temperature (CCT)	Color Coordinates <sup>(3)</sup>		Lumen Output (Typical at 25 °C)
		x	y	
Green	524 nm	0.16	0.708	7.5
Red	620 nm	0.69	0.308	2.5
Yellow	592 nm	0.582	0.413	6.5
Blue	468 nm	0.136	0.062	2
White	5500K	0.332	0.36	7.5

## Construction

**Base, Segments and Audible:** UV stabilized polycarbonate

**Grommet:** TPV

**Mounting Nut:** PBT

**Sealing Gasket:** PVC/NBR/CR

## Mounting

M22 x 1.5 threaded base, maximum torque 2.25 N·m (20 in-lbf)

Mounting nut and sealing gasket included

## Connections

Integral 5-pin or 8-pin M12 male quick-disconnect connector, or integral 1.2 m (3.9 ft) PVC-jacketed cable, depending on model

Models with a quick-disconnect connector require a mating cordset

## Vibration and Mechanical Shock

Meets IEC 60068-2-6 requirements (Vibration: 10 Hz to 55 Hz, 1.0 mm amplitude, 5 minutes sweep, 30 minutes dwell)


Meets IEC 60068-2-27 requirements (Shock: 30G 11 ms duration, half sine wave)

IK07 (EN 60068-2-75 with SMBAMS22RA bracket)

<sup>(3)</sup> Refer to CIE 1931 chromaticity diagram or color chart, to show equivalent color with indicated color coordinates.

## Dimensions

All measurements are listed in millimeters [inches], unless noted otherwise. The measurements provided are subject to change.



Number of colors	Tower Height (H)	
	Non-Audible	Omni-Directional Sealed Audible
2	99.7 mm (3.9 in)	145.6 mm (5.7 in)
3	126.7 mm (5 in)	172.6 mm (6.8 in)
4	153.7 mm (6 in)	199.6 mm (7.9 in)
5	180.7 mm (7.1 in)	226.6 mm (8.9 in)

## Certifications



Banner Engineering BV  
Park Lane, Culliganlaan 2F bus 3  
1831 Diegem, BELGIUM



## Required Overcurrent Protection



**WARNING:** Electrical connections must be made by qualified personnel in accordance with local and national electrical codes and regulations.

Overcurrent protection is required to be provided by end product application per the supplied table.

Overcurrent protection may be provided with external fusing or via Current Limiting, Class 2 Power Supply.

Supply wiring leads < 24 AWG shall not be spliced.

For additional product support, go to [www.bannerengineering.com](http://www.bannerengineering.com).

Supply Wiring (AWG)	Required Overcurrent Protection (A)	Supply Wiring (AWG)	Required Overcurrent Protection (A)
20	5.0	26	1.0
22	3.0	28	0.8
24	2.0	30	0.5

## Accessories

### Cordsets

5-Pin Single-Ended M12 Female Cordsets				
Model	Length	Style	Dimensions	Pinout (Female)
MQDC1-501.5	0.5 m (1.5 ft)	Straight		 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
MQDC1-503	0.9 m (2.9 ft)			
MQDC1-506	2 m (6.5 ft)			
MQDC1-515	5 m (16.4 ft)			
MQDC1-530	9 m (29.5 ft)			
MQDC1-560	18 m (59 ft)			
MQDC1-5100	31 m (101.7 ft)			
MQDC1-506RA	2 m (6.5 ft)			
MQDC1-515RA	5 m (16.4 ft)			
MQDC1-530RA	9 m (29.5 ft)			
MQDC1-560RA	19 m (62.3 ft)	Right-Angle		


8-Pin Single-Ended M12 Female Open-Shielded Cordsets				
Model	Length	Style	Dimensions	Pinout (Female)
MQDC2S-806	2.04 m (6.7 ft)	Straight		 1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red
MQDC2S-815	5.04 m (16.54 ft)			
MQDC2S-830	10.04 m (32.95 ft)			
MQDC2S-850	16 m (52.49 ft)			
MQDC2S-806RA	2 m (6.56 ft)			
MQDC2S-815RA	5 m (16.4 ft)			
MQDC2S-830RA	10 m (32.81 ft)			
MQDC2S-850RA	16 m (52.49 ft)	Right-Angle		

### Brackets

**SMB22A**

- Right-angle bracket with curved slot for versatile orientation
- 12-ga. stainless steel
- Mounting hole for 22 mm sensor


**Hole center spacing:** A to B = 26.0  
**Hole size:** A = Ø 4.6, B = 4.6 x 16.9, C = 22.2



**SMB22FVK**


- V-clamp, flat bracket and fasteners for mounting to pipe or extensions
- Clamp accommodates 28 mm diameter tubing or 1 in. square extrusions
- 22 mm hole for mounting sensor

**Hole size:** A =  $\varnothing$  22.5

**SMB22RAVK**


- V-clamp, right-angle bracket and fasteners for mounting to pipe or extensions
- Clamp accommodates 28 mm diameter tubing or 1 in. square extrusions
- 22 mm hole for mounting sensor

**Hole size:** A =  $\varnothing$  22.5

**SMBAMS22P**


- Flat SMBAMS series bracket with 22 mm hole for mounting sensors
- Articulation slots for 90+° rotation
- 12-ga. (2.6 mm) cold-rolled steel

**Hole center spacing:** A = 26.0, A to B = 13.0  
**Hole size:** A = 26.8 x 7.0, B =  $\varnothing$  6.5, C =  $\varnothing$  22.5

**SMBAMS22RA**


- Right-angle SMBAMS series bracket with 22 mm hole for mounting sensors
- Articulation slots for 90+° rotation
- 12-ga. (2.6 mm) cold-rolled steel

**Hole center spacing:** A = 26.0, A to B = 13.0  
**Hole size:** A = 26.8 x 7.0, B =  $\varnothing$  6.5, C =  $\varnothing$  22.5

**LMBE12RA35**


- Direct mounting of stand-off pipe, with common bracket type
- Zinc-plated steel
- 1/2-14 NPSM nut
- Mounting distance from the wall to the center of the 1/2-14 NPSM nut is 35 mm

**Hole center spacing:** 20.0

**LMBE12RA45**

- Direct mounting of stand-off pipe, with common bracket type
- Zinc-plated steel
- 1/2-14 NPSM nut
- Mounting distance from the wall to the center of the 1/2-14 NPSM nut is 45 mm

**Hole center spacing:** 35.0




## LMB Sealed Right-Angle Bracket

Model	Description	Construction	
LMBE12RA	<b>Pipe-Mount Models:</b> Bracket kit with base, $\frac{1}{2}$ -14 pipe adapter, set screw, fasteners, O-rings, and gaskets. For use with stand-off pipe (listed and sold separately).	Black polycarbonate	

## Elevated Mount System

### Example Assembly



This example uses:

1. Adapter/Cover
2. Pipe
3. Mounting Base (SA-E12M30 shown)

Other compatible parts are listed in the following tables.

### Adapters/Covers



Adapter/Cover Model	Description
SA-M22E12	<ul style="list-style-type: none"> <li>• Streamlined black polycarbonate stand-off pipe adapter/cover</li> <li>• Adapter from 22 mm light base to <math>\frac{1}{2}</math> in. NPSM/DN15 pipe</li> </ul>


### Pipes




Black Anodized Aluminum, $\frac{1}{2}$ in. NPT Pipe Models	Clear Anodized Aluminum, $\frac{1}{2}$ in. NPT Pipe Models	Description
SOP-E12-150A, 150 mm (6 in) long	SOP-E12-150AC, 150 mm (6 in) long	
SOP-E12-300A, 300 mm (12 in) long	SOP-E12-300AC, 300 mm (12 in) long	
SOP-E12-600A, 600 mm (24 in) long	-	
SOP-E12-900A, 900 mm (36 in) long	SOP-E12-900AC, 900 mm (36 in) long	<ul style="list-style-type: none"> <li>• Elevated-use stand-off pipe</li> <li>• Threaded at both ends</li> <li>• Compatible with most industrial environments</li> </ul>

304 Stainless Steel, $\frac{1}{2}$ in. NPT Pipe Models	Description
SOP-E12-150SS, 150 mm (6 in) long	
SOP-E12-300SS, 300 mm (12 in) long	
SOP-E12-600SS, 600 mm (24 in) long	
SOP-E12-900SS, 900 mm (36 in) long	<ul style="list-style-type: none"> <li>• Elevated-use stand-off pipe</li> <li>• Threaded at both ends</li> <li>• Compatible with most industrial environments</li> </ul>


### Bottom Covers and Mounting Bases




Base Adapter/Cover Model	Description
SA-E12M30 - Black acetal	<ul style="list-style-type: none"> <li>Streamlined black acetal or white UHMW mounting base adapter/cover</li> <li>Adapter from <math>\frac{1}{2}</math> in. NPSM/DN15 pipe to 30 mm (1-3/16 in) drilled hole</li> <li>Mounting hardware included</li> </ul>
SA-E12M30C - White UHMW	



Mounting Base Model	Description
SA-F12	<ul style="list-style-type: none"> <li>Die-cast zinc base with black paint</li> <li>Elevated-use stand-off pipes (<math>\frac{1}{2}</math> in, NPSM/DN15)</li> <li>M5 mounting hardware and nitrile gasket included</li> </ul>



Mounting Base Model	Description
SA-F12-3	<ul style="list-style-type: none"> <li>Black polycarbonate</li> <li>Elevated-use stand-off pipes (<math>\frac{1}{2}</math> in, NPSM/DN15)</li> <li>M4 mounting hardware and nitrile blend gasket included</li> </ul>



Foldable Mounting Base Model	Description
SA-FFB12 - Black polycarbonate	<ul style="list-style-type: none"> <li>For use with <math>\frac{1}{2}</math> in. stand-off pipes</li> <li>Stainless steel hardware</li> </ul>
SA-FFB12C - Gray polycarbonate	

## Banner Engineering Corp Limited Warranty

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

**THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEALING OR TRADE USAGE.**

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. **IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.**

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp. Any misuse, abuse, or improper application or installation of this product or use of the product for personal protection applications when the product is identified as not intended for such purposes will void the product warranty. Any modifications to this product without prior express approval by Banner Engineering Corp will void the product warranties. All specifications published in this document are subject to change. Banner reserves the right to modify product specifications or update documentation at any time. Specifications and product information in English supersede that which is provided in any other language. For the most recent version of any documentation, refer to: [www.bannerengineering.com](http://www.bannerengineering.com).

For patent information, see [www.bannerengineering.com/patents](http://www.bannerengineering.com/patents).