




Flasher Solid-State Output

SPECIFICATIONS


OUTPUT RATING	Solid-state, SPST-N.O. 1 amp resistive; 1 amp 25VA @ 24VAC 1 amp 125VA @ 120VAC .5 amp 125VA @ 240 VAC
DELAY PERIOD	Up to 2 hours fixed or external resistor adjustable; see page 77 for standard ranges.
REPEATABILITY	1% maximum; no first cycle effect
LOAD TYPE	Resistive, incandescent, or inductive
SUPPLY VOLTAGE	24, 120 or 240 VAC, 50/60 Hz; $\pm 10\%$
FALSE TRANSFER	No
DUTY CYCLE	50%
ENCLOSURE	Surface mounted; totally encapsulated with a high quality epoxy for environmental protection.
TEMPERATURE RATING	Operate 32° to 131°F (0° to +55°C) Storage -49° to 185°F (-45° to +85°C)
TERMINATIONS	1/4" quick disconnect terminals
WEIGHT	NET: 1.28 oz Shipping: 1.6 oz.

OPERATION


When power is applied, the OFF time begins. Upon completion of the OFF time, the load energizes and the ON time begins. Upon completion of the ON time, the load de-energizes and one cycle is complete. This OFF/ON cycling continues until the voltage is removed. THE OFF TIME ALWAYS EQUALS THE ON TIME.



WIRING



DIMENSIONS (INCHES)



MODEL NUMBER

MODEL NUMBER	TSK		A		C	
SUPPLY VOLTAGE						
24 VAC		24				
120 VAC		120				
240 VAC		240				
TYPE OF OPERATION						
Fixed			F			
External Resistor Adjustable; See page 82 for resistor selection.			R			
DELAY PERIOD						
See page 82 for standard ranges available						

Example: TSG-24-ARC-300—Repeat cycle, 24 VAC, external resistor adjustable from 3 to 300 seconds, UL recognized.