



Product: [1119A](#) 

Inst, 1 Tri #16 Str BC, PVC-NYL Ins E2, OS, Blk PVC Jkt, 600V TC-ER 150V NPLF 90C Dry/Wet

 [Request Sample](#)

Product Description

UL Instrumentation, 1 Triad 16AWG (7x24) Bare Copper, PVC-NYL Insulation E2 Color Code, Overall Beldfoil® Shield, Black PVC Outer Jacket, 600V TC-ER 150V NPLF 90C Dry/Wet SUN RES DIR BUR

Technical Specifications

Product Overview

Suitable Applications:	Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...), low voltage digital control (24v, ...), RTD, control circuits, distributed control system (DCS), programmable logic controller (PLC), Solenoids, Valves, actuators, positioners
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Triad(s)	1	16 AWG	7x24	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Triad(s)	PVC/Nylon - Polyvinyl Chloride + Nylon	0.022 in (0.56 mm)	0.101 in (2.57 mm)	ICEA Chart E2

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.047 in (1.2 mm)	0.315 in (8.00 mm)	Yes

Overall Cable Diameter (Nominal):	0.315 in (8.00 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Max. Current
Triad(s)	4.27 Ohm/1000ft	18 Amps per conductor @ 30°C

Nom Outer Shield DCR:	4.99 Ohm/1000ft (16.4 Ohm/km)
-----------------------	-------------------------------

Voltage

UL Voltage Rating
600 V (TC-ER), 150 V (NPLF)

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C Dry, 90°C Wet	-30°C to 90°C Dry/Wet

Bend Radius

Stationary Min.	Installation Min.
3.8 in (97 mm)	3.8 in (97 mm)

Max. Pull Tension:	129 lbs (58.5 kg)
Bulk Cable Weight:	63 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Burial
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, T-29-520, IEEE 1202 FT4
NEC / UL Compliance:	Article 336, Article 760, NPLF, TC-ER
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.605 Revision Date: 04-10-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1119A 010500	Black	Reel	500 ft	612825107149	C Z
1119A 0101000	Black	Reel	1,000 ft	612825107118	C Z
1119A 01010000	Black	Reel	10,000 ft	612825107125	C Z

Footnote:	C - CRATE REEL PUT-UP., Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
-----------	--

© 2026 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.