

Product: [1152A](#)


Broadband Coax, Series 6, 18 AWG Solid BCCS, Quad Shield, FEP Jkt, CMP

Product Description

Broadband Coax, Series 6, 18 AWG Solid Bare Copper Covered Steel Conductor, FEP Insulation, Foil + 60% Tinned Copper Braid + Foil + 40% Tinned Copper Braid Shield, FEP Jacket, CMP

Technical Specifications
Product Overview

Suitable Applications:	Broadband, Cable Television (CATV), RF drop cable, Over-The-Air (OTA) antennas
------------------------	--

Construction Details

RG Type:	6
----------	---

Conductor

Element	Size	Stranding	Nom. Diameter	Material
Coax(es)	18 AWG	Solid	0.040 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.170 in (4.32 mm)	White

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Tinned Copper (TC)		60%
3	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
4	Braid	Tinned Copper (TC)		45%

Outer Jacket

Material	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.273 in (6.93 mm)

Overall Cable Diameter (Nominal): 0.273 in (6.93 mm)

Electrical Characteristics
Return Loss

Frequency	Min. Structural Return Loss
10 - 400 MHz	20 dB

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.3 dB/100ft
10 MHz	0.66 dB/100ft
50 MHz	1.6 dB/100ft
100 MHz	2.2 dB/100ft
200 MHz	3.0 dB/100ft
400 MHz	4.6 dB/100ft
700 MHz	6.6 dB/100ft

900 MHz	7.7 dB/100ft
1000 MHz	8.2 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
28 Ohm/1000ft (92 Ohm/km)	1.8 Ohm/1000ft (5.9 Ohm/km)	16.5 pF/ft (54.1 pF/m)	75 Ohm	82%

Voltage

UL Voltage Rating
300 V (CMP), (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating
200°C	-70°C to +200°C

Bend Radius

Stationary Min.	Installation Min.
2.75 in (69.9 mm)	2.75 in (69.9 mm)

Max. Pull Tension: 192 lbs (87.1 kg)

Bulk Cable Weight: 45 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor, Outdoor, Aerial - When supported by messenger wire, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262, FT6
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ANSI/SCTE 74

Product Notes

Notes:	For use in indoor plenum environments but also suitable for outdoor and underground applications.
--------	---

History

Update and Revision:	Revision Number: 0.466 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1152A A8R500	Beige, Snow	Reel	500 ft	612825107491	C
1152A A8R1000	Beige, Snow	Reel	1,000 ft	612825107484	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.