



Product: [1815R](#) 

Audio Snake Cable, 4 Pr #22 Str TC, Ind. Shielded & Jacketed, O/A Foil, PVC Jkt, CMR

Product Description

Audio Snake Cable, 4 Pair 22 AWG (7 x 30) Tinned Copper, PP Insulation, Individually Foil Shielded and PVC Jacketed, Overall Beldfoil® Shield, PVC Jacket, Ripcord, CMR

Technical Specifications

Product Overview

Suitable Applications:	Multi-channel interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles; Live events or studio sound; Analog audio
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	4	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
Pair(s)	PP - Polypropylene	0.010 in (0.25 mm)	0.05 in (1.3 mm)	Black & Red	
				Brown, Red, Orange, Yellow	The Colors represented in this rows are for Inner Jacket colors

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC	Individual pair tapes are adhered to their inner jackets for easy stripping

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (19x30) TC

Inner Jacket

Element	Material	Nom. Thickness	Nom. Diameter
Pair(s)	PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.133 in (3.38 mm)

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.030 in (0.76 mm)	0.384 in (9.75 mm)	Yes

Overall Cable Diameter (Nominal):	0.384 in (9.75 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Inductance	Nom. Velocity of Prop.	Max. Current
Pair(s)	14.8 Ohm/1000ft	31 pF/ft (100 pF/m)	56 pF/ft (180 pF/m)	50 Ohm	0.18 µH/ft (0.59 µH/m)	66%	1.45 Amps per conductor @ 25°C

Nom Outer Shield DCR:	11.8 Ohm/1000ft (38.7 Ohm/km)
-----------------------	-------------------------------

Voltage

UL Voltage Rating

300 V (CMR)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

Bend Radius

Stationary Min.	Installation Min.
3.8 in (97 mm)	3.8 in (97 mm)

Max. Pull Tension:	109 lbs (49.4 kg)
Bulk Cable Weight:	84 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMR
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	1815P

History

Update and Revision:	Revision Number: 0.503 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1815R 010500	Black	Reel	500 ft	612825123484	C
1815R 0101000	Black	Reel	1,000 ft	612825123477	C
1815R 0105000	Black	Reel	5,000 ft	612825431206	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.