



Product: [29537](#) 

VFD 300% Gnd, 3C+G #12 Str TC, XLPE Ins+PVC Gnd, OS+TC Brd w/#12 TC Drain, Blk PVC Jkt, 2000V TC-ER 90C Dry/Wet 2000V Flexible Motor Supply Cable WTTC

 [Request Sample](#)

Product Description

Belden 300% Ground Flexible VFD, 3 Conductor 12AWG (65x30) Tinned Copper, XLPE Insulation M4 Color Code+PVC Insulated Ground, Overall Beldfoil®+Tinned Copper Braid(85%) Shield w/12AWG Tinned Copper Drain, Black PVC Outer Jacket, 2000V TC-ER 90C Dry/Wet 2000V Flexible Motor Supply Cable WTTC 1000V CSA AWM I/II A/B 600V CIC TC SUN RES DIR BUR Oil Resistant

Technical Specifications

Product Overview

Suitable Applications:	Variable Frequency Drives (VFD); AC Motor and Drive Systems; High voltage requirements
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	12 AWG	65x30	TC - Tinned Copper
Ground Wire	1	12 AWG	65x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	XLPE - Cross-Linked Polyethylene (Thermoset)	0.066 in (1.7 mm)	0.225 in (5.72 mm)	ICEA Chart M4
Ground Wire	XLPE - Cross-Linked Polyethylene (Thermoset)	0.066 in (1.7 mm)	0.225 in (5.72 mm)	Green/Yellow Stripe

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Tri-Laminate (Alum+Poly+Alum)	100%	12 AWG (65x30) TC
Braid	Tinned Copper (TC)	85%	

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.073 in (1.9 mm)	0.723 in (18.4 mm)	Yes

Overall Cable Diameter (Nominal):	0.723 in (18.4 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Inductance	Nom. Velocity of Prop.	Max. Current
Conductor(s)	1.569 Ohm/1000ft	54 pF/ft (180 pF/m)	97 pF/ft (320 pF/m)	44 Ohm	0.197 µH/ft (0.646 µH/m)	55%	30 Amps per Conductor at 30°C
	1.72 Ohm/1000ft (5.64 Ohm/km)						30 Amps per Conductor at 30°C

Nom Outer Shield DCR:	0.68 Ohm/1000ft (2.2 Ohm/km)
-----------------------	------------------------------

Voltage

UL Voltage Rating
2000 V (TC, C(UL) TC), 1000 V (WTTC, UL Flexible Motor Supply Cable, CSA AWM I/II A/B)

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C Dry, 90°C Wet	-40°C To +90°C

Bend Radius

Stationary Min.	Installation Min.
8.7 in (220 mm)	8.7 in (220 mm)

Max. Pull Tension:	7922 lbs (3593 kg)
Bulk Cable Weight:	336 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 UL Loading, FT4, IEEE 1202 FT4
NEC / UL Compliance:	Article 336, TC-ER, WTTC, UL Flexible Motor Supply Cable
AWM Compliance:	AWM I/II A/B
CEC / C(UL) Compliance:	.
ICEA Compliance:	S-95-658
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	P-07-KA070003-MSHA

History

Update and Revision:	Revision Number: 0.541 Revision Date: 02-20-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
29537 0101000	Black	Reel	1,000 ft	612825138419
29537 0105000	Black	Reel	5,000 ft	612825138426

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.