



Product: [29730C](#) 

VFD, 3C #2/0 Str BC XLPE Ins + #5 Symm. Seg. Gnd (3 of #10) Str BC, CTS, Blk PVC Jkt, 2000V TC-ER 90C Dry/Wet 1000V CSA AWM I/II A/B

Product Description

Belden Basics VFD, 3 Conductor 2/0AWG (19x12) Bare Copper XLPE Insulation M4 Color Code + 5AWG Symmetrical Segmented Ground (3 of 10AWG) Bare Copper Stranded, Overall Dual Copper Tapes Helically Applied Shield, Black PVC Outer Jacket, 2000V TC-ER 90C Dry/Wet 1000V CSA AWM I/II A/B SUN RES DIR BUR Oil Resistant

Technical Specifications

Product Overview

Suitable Applications:	Variable Frequency Drives (VFD); AC Motor and Drive Systems; High voltage requirements
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material	Notes
Conductor(s)	3	2/0 AWG	19x12	BC - Bare Copper	ASTM B3 Copper B8 Class B Stranding
Ground	3	10 AWG	7x18	BC - Bare Copper	Segmented Grounds

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	XLPE - Cross-Linked Polyethylene (Thermoset)	0.095 in (2.4 mm)	0.592 in (15.0 mm)	Black and Numbered
Ground	No Insulation			

Outer Shield

Shield Type	Material	Coverage
Helical Tape	Bare Copper (BC)	100%
Helical Tape	Bare Copper (BC)	100%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.083 in (2.1 mm)	1.454 in (36.93 mm)	Yes

Overall Cable Diameter (Nominal):	1.454 in (36.93 mm)
-----------------------------------	---------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Inductance	Nom. Velocity of Prop.	Max. Current
Conductor(s)	0.083 Ohm/1000ft (0.27 Ohm/km)	26 pF/ft (85 pF/m)	47 pF/ft (150 pF/m)	71 Ohm	0.141 µH/ft (0.463 µH/m)	55%	195 Amps per Conductor at 30°C

Voltage

UL Voltage Rating
2000 V (TC), 1000 V (CSA AWM I/II A/B)

Mechanical Characteristics

Temperature

UL Temperature	Operating
----------------	-----------

90°C Dry, 90°C Wet	-40°C To +90°C
--------------------	----------------

Bend Radius

Stationary Min.	Installation Min.
17.4 in (442 mm)	17.4 in (442 mm)

Max. Pull Tension:	4893 lbs (2219 kg)
Bulk Cable Weight:	1810 lbs/1000ft (2690 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 UL Loading, 1202, 383 Vertical Tray Flame Test (70,000 BTU)
NEC / UL Compliance:	Article 336, TC-ER, RHW-2
AWM Compliance:	I/II A/B
ICEA Compliance:	S-95-658
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	P-07-KA070003-MSHA

History

Update and Revision:	Revision Number: 0.79 Revision Date: 09-07-2025
----------------------	---

Part Numbers

Variants

Item #	Putup Type	UPC
29730C 0101000	Reel	612825445616
29730C 0102500	Reel	612825445623

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.