

Product: [34402](#)

Lead Wire, #2 Str TC, CSPE Ins, AWM 3192
[Request Sample](#)
Product Description

Low Temp Rubber Lead Wire, 2AWG (163x24) Tinned Copper, CSPE Insulation, AWM 3192 CSA TYPE CL1052 600V 105C

Technical Specifications
Product Overview

Suitable Applications:	Class 130(B) motor lead systems, internal wiring of appliances, oil resistance applications
------------------------	---

Construction Details
Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	2 AWG	163x24	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
CSPE - Chlorosulphonated Polyethylene	0.068 in (1.7 mm)	0.454 in (11.5 mm)

Overall Cable Diameter (Nominal): 0.454 in (11.5 mm)

Electrical Characteristics
Electricals

Nom. Conductor DCR	Max. Current
0.180 Ohm/1000ft	228.8 Amps per Conductor at 30°C

Voltage

UL Voltage Rating	Voltage Rating
600 V (AWM 3192)	300 V (CSA CL-1052)

Mechanical Characteristics
Temperature

UL Temperature	Operating
105°C	-30°C To +105°C

Bend Radius

Stationary Min.	Installation Min.
4.54 in (115 mm)	4.54 in (115 mm)

Max. Pull Tension: 824.6 lbs (374.0 kg)

Bulk Cable Weight: 263 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Oil Resistance
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	Horizontal flame
AWM Compliance:	AWM 3192

CEC / C(UL) Compliance:	CL-1052
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Separator tape over conductor.
--------	--------------------------------

History

Update and Revision:	Revision Number: 0.495 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants					
Item #	Color	Putup Type	Length	UPC	Footnote
34402 010100	Black	Reel	100 ft	612825143680	C
34402 010250	Black	Reel	250 ft	612825143697	C F
34402 010500	Black	Reel	500 ft	612825143703	C F

Footnote:	C - CRATE REEL PUT-UP., F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.
-----------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.