



Product: [6341PT](#)

Thermostat & Control, #18-2pr, TC, Indiv. Foil, CMP

Product Description

Thermostat & Control Cable, Plenum-CMP, 2-18 AWG stranded tinned copper pairs with foam FEP insulation, Individually Beldfoil® shielded and Flamarrest® jacket

Technical Specifications

Product Overview

Suitable Applications:	Thermostat, Control, Noisy Environment
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
18	7x26	TC - Tinned Copper	2

Conductor Count:	4
------------------	---

Insulation

Material
FEP - Fluorinated Ethylene Propylene (Foam)

Color Chart

Number	Color
1	Black & White
2	Green & Red

Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	18	7x26

Outer Jacket

Material	Material Trade Name	Nominal Diameter
PVC - Polyvinyl Chloride	Flamarrest®	0.28 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
6.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
13.7 pF/ft

Inductance

Nominal Inductance
0.21 µH/ft

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
78 ns/100m	78%

High Frequency

Max./Min. Input Impedance (unFitted)
100 ± 10 Ohm

Current

Max. Recommended Current [A]
8.1 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temperature Rating:	75°C
Operating Temperature Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	56 lbs/1000ft
Maximum Recommended Pulling Tension:	134 lbs
Minimum Minor Axis Bend Radius:	2.8 in

Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262 Plenum Flame Test (UL910)
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Related Part Numbers

Variants

Item #	Color	UPC
6341PT 0011000	Brown	612825176299

Footnote: C - CRATE REEL PUT-UP.

History

Update and Revision:	Revision Number: 0.332 Revision Date: 02-03-2025
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.