



Product: [7136WS](#) 

MachFlex™, 3+1G C #14 Str BC, PVC-NYL Ins, OA TC Brd, TPE Jkt, TPE Jkt, 1000V WTTTC, 600V TC-ER

 [Request Sample](#)

Product Description

MachFlex™ for High Flex, 3+1G Conductor 14AWG (259(7x37)x38) Bare Copper, PVC-NYL Insulation, Overall Tinned Copper Braid(85%) Shield, TPE Inner Jacket, TPE Outer Jacket, 1000V WTTTC, 600V TC-ER

Technical Specifications

Product Overview

Suitable Applications:	Robotics, Robot, Continuous Flex
------------------------	----------------------------------

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	14 AWG	259x38	BC - Bare Copper
Ground Wire	1	14 AWG	259x38	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC/Nylon - Polyvinyl Chloride + Nylon	0.021 in (0.53 mm)	0.122 in (3.10 mm)	Black and Numbered
Ground Wire	PVC/Nylon - Polyvinyl Chloride + Nylon	0.021 in (0.53 mm)	0.122 in (3.10 mm)	Green/Yellow

Outer Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	86%

Inner Jacket

Separator	Material	Nom. Thickness	Nom. Diameter	Color
non-Woven Tape	TPE - Thermoplastic Elastomer	0.030 in (0.76 mm)	0.360 in (9.14 mm)	Orange

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
TPE - Thermoplastic Elastomer	0.053 in (1.3 mm)	0.488 in

Overall Cable Diameter (Nominal): 0.488 in

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Max. Current
Conductor(s)	2.62 Ohm/1000ft	29 Amps per Conductor at 30°C
Ground Wire	2.73 Ohm/1000ft (8.96 Ohm/km)	46.4 Amps per Conductor at 30°C

Nom Outer Shield DCR: 3.3 Ohm/1000ft (11 Ohm/km)

Voltage

UL Voltage Rating
1000 V (WTTTC), 600 V (TC-ER)

Mechanical Characteristics

Temperature

UL Temperature	Operating
UL : 90°C Dry, 75°C Wet; AWM 20328 : 105°C	-40°C To 105°C

Bend Radius

Stationary Min.	Installation Min.
1.95 in (49.5 mm)	2.44 in

Max. Pull Tension:	190 lbs (86 kg)
Bulk Cable Weight:	167 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor, Sunlight Resistance, UV Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL1685 UL Loading, IEEE 1202 FT4
NEC / UL Compliance:	Article 336
AWM Compliance:	AWM 20328, AWM I/II A/B
CEC / C(UL) Compliance:	CIC, TC.
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.195 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
7136WS 003250	Orange	Reel	250 ft	612825182559	C
7136WS 0031000	Orange	Reel	1,000 ft	612825182542	C
7136WS 0035000	Orange	Reel	5,000 ft	612825182566	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.