

METRIC MEASUREMENT VERSION

76610TS Multi-Conductor - 300V Shielded, Continuous Flexing Data Applications Up to 6 Million FLEflex Life Cycles


 For more Information
 please call

1-800-Belden1

General Description:

24 AWG stranded (10x34) tinned copper conductors, PVC insulation, aluminum/polyester foil shield, tinned copper braid shield, 85% coverage, oil-resistant overall PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
10	24	10x34	TC - Tinned Copper	0.610

Total Number of Conductors:

20

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)	Dia. (mm)
PVC - Polyvinyl Chloride	0.254	1.118

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Foil Shield	Alum/Mylar	100.000
Braid	Tinned Copper	85.000

Outer Shield Drain Wire AWG:

Component	AWG	Stranding	Drain Wire Conductor Material
Drain Wire	26	7x34	TC - Tinned Copper

Outer Shield Separator Material:

Tissue Tape, 25&#37; Overlap, Min.

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.143

Overall Cable

Overall Nominal Diameter:

10.846 mm

Pair

Pair Color Code Chart:

Number	Color
1	BLACK-RED
2	BLACK-WHITE
3	BLACK-GREEN
4	BLACK-BLUE
5	BLACK-BROWN
6	BLACK-YELLOW
7	BLACK-ORANGE
8	RED-GREEN
9	RED-WHITE
10	RED-BLUE

Mechanical Characteristics (Overall)

Bulk Cable Weight: 142.867 Kg/Km

Max. Recommended Pulling Tension: 324.719 N

Min. Bend Radius/Minor Axis: 109.220 mm

Min. Bend/Installation: 109.220 mm

Min. Bend Radius (Continuous Flexing): 162.560 mm

Flex Cycle Rating: 6 Million Flexes

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC(UL) Specification: CM

AWM Specification: UL Style 20006

METRIC MEASUREMENT VERSION

76610TS Multi-Conductor - 300V Shielded, Continuous Flexing Data Applications Up to 6 Million FLeX Life Cycles

CSA Specification:	600 V AWM I/II A/B
EU Directive 2011/65/EU (ROHS II):	Yes
Other Specification:	AWM/STYLE 10002, AWM/STYLE 2661, CM, AWM I/II A/B, C(UL) TYPE CMG, FT4, EU Low Voltage Directive 2014/35/EC, EU Directive 2011/65/EU(RoHS2)

Flame Test

CSA Flame Test:	FT4
-----------------	-----

Suitability

Sunlight Resistance:	Yes
----------------------	-----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Description	Impedance (Ohm)
Characteristic Impedance	82.000

Nom. Inductance:

Inductance (μH/m)
0.623

Nom. Capacitance Cond. to Other Cond. & Ground:

Description	Freq. (kHz)	Capacitance (pF/m)
Mutual Capacitance	1.000	75.791
Ground Capacitance	1.000	137.802

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
98.430

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
6.923

Notes (Overall)

Notes: Temperature Range -10 to 105°C(static), +5 to 105°C (dynamic)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 0 Revision Date: 09-27-2017

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.