



Product: [7700A](#) 

75 Ohm Analog Video Coax, Dual Ultra-miniature RG-59, 30 AWG Str TC, 95% TC French Braids, Flamarrest® Jkt, CMP, Flexible

Product Description

75 Ohm Analog Video Coax, Dual Ultra-miniature RG-59, 30 AWG (7x38) Tinned Copper Conductors , FEP Insulation, 95% Tinned Copper French Braid Inner Shields, Flamarrest® Jacket, CMP, Flexible

Technical Specifications

Product Overview

Suitable Applications:	S-Video, Standard analog video
------------------------	--------------------------------

Construction Details

RG Type:	Ultra-miniature 59
----------	--------------------

Conductor

Size	Stranding	Nom. Diameter	Material
30 AWG	7x38	0.012 in	TC - Tinned Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
PFA - Perfluoroalkoxy (Foam)	0.053 in (1.3 mm)	White

Inner Shield

Shield Type	Material	Coverage
French Braid	Tinned Copper (TC)	95%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.107 x .215 in

Overall Cable Diameter (Nominal):	0.107 in (2.72 mm)
-----------------------------------	--------------------

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.7 dB/100ft
5 MHz	1.7 dB/100ft
10 MHz	2.3 dB/100ft
30 MHz	4.1 dB/100ft
50 MHz	5.3 dB/100ft
100 MHz	7.6 dB/100ft
200 MHz	11.8 dB/100ft
400 MHz	17.6 dB/100ft
700 MHz	24.2 dB/100ft
900 MHz	28.0 dB/100ft
1000 MHz	29.8 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
--------------------	-----------------------	---------------------------------	-------------------------------	------------------------

92.6 Ohm/1000ft	7.5 Ohm/1000ft (25 Ohm/km)	17.3 pF/ft (56.8 pF/m)	75 Ohm	78%
-----------------	----------------------------	------------------------	--------	-----

Voltage

UL Voltage Rating	Voltage Rating
300 V (CMP)	300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

Bend Radius

Installation Min.
2.2 in (56 mm)

Max. Pull Tension:	12 lbs (5.4 kg)
Bulk Cable Weight:	20 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Aerial - Black only, When supported by messenger wire
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP.
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	1807A

History

Update and Revision:	Revision Number: 0.440 Revision Date: 02-20-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
7700A B59500	Black, Matte	Reel	500 ft	612825415879	
7700A B591000	Black, Matte	Reel	1,000 ft	612825188223	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.