



Product: [7971A](#) 

DataTuff® 6, 4 Bonded-Pr #22 Sol BC, PO Ins, X-spline, PVC Jkt, OS+TC Brd, PVC Jkt, PLTC, CMR, CMX Outdoor

Product Description

Industrial Ethernet Cat 6, 4 Bonded-Pair 22AWG (Solid) Bare Copper, PO Insulation, X-spline, PVC Inner Jacket, Overall Beldfoil®+Tinned Copper Braid(80%) Shield, PVC Outer Jacket, PLTC, CMR, CMX Outdoor

Technical Specifications

Product Overview

Suitable Applications:	Power-limited tray, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
22 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair:	Yes
--------------	-----

Inner Jacket

Separator	Material	Nom. Diameter	Ripcord
	PVC - Polyvinyl Chloride	0.305 in (7.75 mm)	Yes
Center Member (Patented X-Spline®)			

Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	80%

Outer Jacket

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.425 in (10.8 mm)	No

Overall Cable Diameter (Nominal):	0.425 in (10.8 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
56.5 Ohm/km (17.2 Ohm/1000ft)	330 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	45 ns/100m	68%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Min. TCL [dB]
1	2	74.3	72.3	72.3	70.3	67.8	64.8	20	100 ± 15	40
4	3.78	65.28	63.28	61.5	59.5	55.71	52.71	23.01	100 ± 15	40
8	5.32	60.77	58.77	55.45	53.45	49.69	46.69	24.52	100 ± 15	40
10	5.95	59.31	57.31	53.36	51.36	47.75	44.75	25	100 ± 15	40
16	7.55	56.25	54.25	48.7	46.7	43.67	40.67	25	100 ± 15	37.96
20	8.47	54.8	52.8	46.33	44.33	41.73	38.73	25	100 ± 15	36.99
25	9.51	53.35	51.35	43.84	41.84	39.79	36.79	24.32	100 ± 15	36.02
31.25	10.67	51.89	49.89	41.22	39.22	37.86	34.86	23.64	100 ± 15	35.05
62.5	15.38	47.38	45.38	31.99	29.99	31.83	28.83	21.54	100 ± 15	32.04
100	19.8	44.31	42.31	24.51	22.51	27.75	24.75	20.11	100 ± 15	30
155	25.16	41.46	39.46	16.3	14.3	23.95	20.95	18.77	100 ± 15	28.1
200	28.98	39.8	37.8	10.82	8.82	21.73	18.73	18	100 ± 15	26.99
250	32.85	38.35	36.35	5.5	3.5	19.79	16.79	17.32	100 ± 15	26.02

Voltage

UL Voltage Rating
300 V (PLTC, CMR/CMX-Outdoor), 600 V (AWM)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
75°C	-40°C To +75°C	-40°C To +75°C	-40°C To +60°C

Bend Radius

Installation Min.	Flexing Min.
2.6 in (66 mm)	5.1 in (130 mm)

Bend Radius Table Notes:	Theses cable are rated for both indoor and outdoor applications. For outdoor installations, the continuous flexing bend radius must be applied for outdoor use. Outdoor installations are susceptible to frequent movement due to environmental factors.
Bulk Cable Weight:	87.5 lbs/1000ft (130 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL 1685 Flame only
CPR Compliance:	CPR Euroclass: Fca
NEC / UL Compliance:	Article 800, Article 725, PLTC - CMR/CMX Outdoor
AWM Compliance:	AWM 21047
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical system.
--------	---

History

Update and Revision:	Revision Number: 0.83 Revision Date: 02-20-2026
----------------------	---

Part Numbers

Variants

Item #
7971A 0101000
7971A 0105000

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.