



50m cable ring PUR/PVC 18x0.75 GY

17 num. + GN/YE
Art.No.: 8000-00000-5335000
Weight: 11.700 kg
Country of origin: FR
Model designation: MVZ-L 50M 533
4-way distribution box M12, UNIVERSAL
PUR/PVC
18× 0.75 mm²

Link to Product

Illustration



Product may differ from Image



Header

Material short text MVZ-L 50M 533

Commercial data

URL Webshop	https://shop.murrelektronik.com/8000-00000-5335000
GTIN	4048879300025
ECLASS-6.0	27062011
ECLASS-6.1	27061801
ECLASS-7.0	27061801
ECLASS-7.1	27061801
ECLASS-8.0	27061801
ECLASS-8.1	27061801
ECLASS-9.0	27061801
ECLASS-9.1	27061801
ECLASS-10.0.1	27061801
ECLASS-10.1	27061801
ECLASS-11.0	27061801
ECLASS-11.1	27061801
ECLASS-12.0	27061801
ECLASS-13.0	27061801

ECLASS-14.0	27061801
ETIM-5.0	EC001578
ETIM-6.0	EC001578
customs tariff number	85444995
EAN	4048879300025
Packaging unit	1

Installation | Cable

Cable identification	533
Stranding	1 × Wires
Amount stranding (type 2)	1
Stranding (type 2)	1 × Wires
Filler	Yes
Cable weight	234 g/m
Material wire insulation	PVC
Amount wires	18
Outer diameter insulation	1,9 mm
Outer diameter tolerance core insulation	± 0,05 mm
Ingredient freeness wire insulation	lead-free, CFC-free
Printing color of wire insulation	white (isolation black)
Amount strands (wire)	24
Diameter of single wires	0,2 mm
Conductor crosssection (wire)	0,75 mm²
Material conductor wire	Stranded copper wire, bare
Conductor type (wire)	Strand class 5
Outer-diameter (jacket)	11,7 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	PUR
Freedom from ingredients (jacket)	lead-free, CFC-free, halogen-free
Conductor resistance (wire)	25 Ω/km @ 20 °C
Max. rated voltage (conductor - ground)	300 V
Max. rated voltage (conductor - conductor)	500 V
Withstand voltage (wire - wire)	4 kV @ 60 s
Withstand voltage (wire - jacket)	4 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity max. (wire)	7,8 A
Operating temperature min. (static)	-40 °C
Operating temperature max. (static)	80 °C
Operating temperature min. (dynamic)	-5 °C
Operating temperature max. (dynamic)	70 °C
Other resistances	resistant to hydrolysis, resistant to microbes
Bending radius (fixed)	6 × Outer diameter
Bending radius (dynamic)	20 × Outer diameter

Connection type 1

Family construction form	free cable end
No. of poles	18
Color contact carrier	gray