

**Product:** [8233P](#) 



Triax, RG11, 14 AWG Solid BC, Double BC Braids, PVDF Jkt, CMP

## Product Description

Triax, RG11, 14 AWG Solid Bare Copper Conductor, FEP Insulation, 95% Bare Copper Braid Shield, PVDF Insulation 80% Bare Copper Braid Shield, PVDF Jacket, CMP

## Technical Specifications

### Product Overview

Suitable Applications:	Analog Video; Interconnect camera to CCU (camera control unit)
------------------------	----------------------------------------------------------------

### Construction Details

RG Type:	11
----------	----

#### Conductor

Size	Stranding	Nom. Diameter	Material
14 AWG	Solid	0.064 in	BC - Bare Copper

#### Insulation

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.285 in (7.24 mm)	White

#### Inner Shield

Layer	Shield Type	Material	Coverage
1	Braid	Bare Copper (BC)	95%

#### Inner Jacket

Material	Nom. Diameter
PVDF - Polyvinylidene Fluoride	0.350 in (8.89 mm)

#### Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Braid	Bare Copper (BC)	80%

#### Outer Jacket

Material	Nom. Diameter
PVDF - Polyvinylidene Fluoride	0.408 in (10.4 mm)

Overall Cable Diameter (Nominal):	0.408 in (10.4 mm)
-----------------------------------	--------------------

## Electrical Characteristics

#### Return Loss

Frequency	Min. Return Loss
5 - 850 MHz	21 dB
850 - 4500 MHz	15 dB

#### Attenuation

Frequency	Nom. Attenuation
1 MHz	0.09 dB/100ft

3.6 MHz	0.28 dB/100ft
10 MHz	0.47 dB/100ft
71.5 MHz	1.33 dB/100ft
135 MHz	1.90
270 MHz	2.94 dB/100ft
360 MHz	3.42 dB/100ft
540 MHz	4.46 dB/100ft
720 MHz	5.41 dB/100ft
750 MHz	5.51 dB/100ft
1000 MHz	6.74 dB/100ft
1500 MHz	9.03 dB/100ft
2250 MHz	11.30 dB/100ft
3000 MHz	12.54 dB/100ft
3000 MHz	17.00 dB/100ft
4000 MHz	27.45 dB/100ft

#### Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
2.5 Ohm/1000ft	1.6 Ohm/1000ft (5.2 Ohm/km)	1.4 Ohm/1000ft (4.6 Ohm/km)	16.5 pF/ft (54.1 pF/m)	75 Ohm	80%

#### Voltage

UL Voltage Rating
300 V (CMP)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
125°C	-15°C to +125°C

#### Bend Radius

Installation Min.
4.0 in (100 mm)

Max. Pull Tension:	170 lbs (77 kg)
Bulk Cable Weight:	132 lbs/1000ft

### Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	8233A

### History

Update and Revision:	Revision Number: 0.452 Revision Date: 02-20-2026
----------------------	--------------------------------------------------

### Part Numbers

#### Variants

Item #	Color	Putup Type	Length	UPC
8233P 010500	Black	Reel	500 ft	612825440031
8233P 0101000	Black	Reel	1,000 ft	612825196662
8233P 0105000	Black	Reel	5,000 ft	612825354970

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.