





EXACT12, 4XM12, 4 POLE
Conn.M12 8pole
Art.No.: 8000-84470-0000000
Weight: 0.107 kg
Country of origin: DE
Model designation: MVP12N-NS4V
4-way
4-pole (port 3+4)
5-pole (port 1+2)
M12 plug connection, 8-pole
with LED for digital PNP-signals 24 V DC
Plastic housings with good resistance against chemicals and oils.
[**Link to Product**](#)
Illustration




Product may differ from Image



Header

Material short text MVP12N-NS4V

Commercial data

URL Webshop	https://shop.murrelektronik.com/8000-84470-0000000
GTIN	4048879323086
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879323086
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Current operating per contact max.	2 A
Total current max.	2 A

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67, IP65
-------------------------------------	------------

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	70 °C
----------------------------	-------

Connection type 2

Family construction form	M12
--------------------------	-----

No. of poles	8
--------------	---

Coding	A
--------	---

Gender	male
--------	------

Color contact carrier	black
-----------------------	-------

PIN 5	+
-------	---

Family construction form	M8
--------------------------	----

No. of poles	4
--------------	---

Coding	A
--------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

PIN 1	+
-------	---

PIN 2	n.c.
-------	------

PIN 3	-
-------	---

PIN 4	NO S 1
-------	--------