



Product: [8255](#) 

93Ω RG-62B/U Type, #24 Str BCCS, Semi-solid PE, BC Braid,
Non-Contaminating PVC Jkt, CMX

Product Description

Coax 93Ω RG-62B/U Type, 24 AWG (7x32) bare copper-covered steel conductor, semi-solid polyethylene insulation, bare copper braid shield (95% coverage), non-contaminating PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Computer, Instrumentation
------------------------	---------------------------

Construction Details

RG Type:	62
----------	----

Conductor

Size	Stranding	Nom. Diameter	Material
24 AWG	Stranded	0.024 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code	Notes
PE - Polyethylene (Semi-Solid)	0.146 in (3.71 mm)	White	Solid PE monofilament spiral around conductor. Solid PE tube over monofilament

Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Braid	Bare Copper (BC)	95%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride (Non-Contaminating)	0.242 in (6.15 mm)

Overall Cable Diameter (Nominal):	0.242 in (6.15 mm)
-----------------------------------	--------------------

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.31 dB/100ft
10 MHz	0.90 dB/100ft
50 MHz	2.00 dB/100ft
100 MHz	2.90 dB/100ft
200 MHz	4.20 dB/100ft
400 MHz	6.10 dB/100ft
700 MHz	8.60 dB/100ft
900 MHz	10.10 dB/100ft
1000 MHz	11.0 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
59.0 Ohm/1000ft	2.9 Ohm/1000ft (9.5 Ohm/km)	13.5 pF/ft (44.3 pF/m)	93 Ohm	84%

Voltage

UL Voltage Rating	Voltage Rating
300 V (CMX), 30 V (UL AWM 1354)	750 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C (UL AWM 1354)	-40°C to +85°C

Bend Radius

Installation Min.
2.4 in (61 mm)

Max. Pull Tension:	75 lbs (34 kg)
Bulk Cable Weight:	33 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, UV Resistance, Aerial - When supported by messenger wire
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1581
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	CMX
AWM Compliance:	AWM 1354
CEC / C(UL) Compliance:	CMX.
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.611 Revision Date: 02-20-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8255 010500	Black	Reel	500 ft	612825197331	
8255 0101000	Black	Reel	1,000 ft	612825197324	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.