



Product: [82761](#) 

Electronic, 2 C #22 Str TC, FEP Ins, OS, PVC Jkt, CMP

 [Request Sample](#)

Product Description

Electronic Cable, 2 Conductor 22AWG (7x30) Tinned Copper, FEP Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications:	indoor plenum applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	FEP - Fluorinated Ethylene Propylene	0.007 in (0.18 mm)	0.042 in (1.1 mm)	Black & Red

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.014 in (0.36 mm)	0.118 in (3.00 mm)

Overall Cable Diameter (Nominal): 0.118 in (3.00 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Inductance	Max. Current
Pair(s)	15 Ohm/1000ft	35 pF/ft (110 pF/m)	67 pF/ft (220 pF/m)	42 Ohm	0.16 µH/ft (0.52 µH/m)	2.8 Amps per Conductor at 25°C

Nom Outer Shield DCR: 18.2 Ohm/1000ft (59.7 Ohm/km)

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.

1.18 in (30.0 mm) 1.18 in (30.0 mm)

Max. Pull Tension: 27 lbs (12 kg)

Bulk Cable Weight: 11 lbs/1000ft

Standards and Compliance

Environmental Suitability: Indoor - Plenum, Indoor

Flammability / Reaction to Fire: NFPA 262, UL 910 (Plenum), FT6

CPR Compliance: CPR Euroclass: Eca

NEC / UL Compliance: Article 800, CMP

CEC / C(UL) Compliance: CMP

European Directive Compliance: EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

UK Regulation Compliance: UKCA Mark

APAC Compliance: China RoHS II (GB/T 26572-2011)

Non-Plenum Number: 8761

History

Update and Revision: Revision Number: 0.551 Revision Date: 09-07-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
82761 877U500	Natural	UnReel	500 ft	612825197775	
82761 8771000	Natural	Reel	1,000 ft	612825197782	C
82761 877U1000	Natural	UnReel	1,000 ft	612825197768	
82761 8775000	Natural	Reel	5,000 ft	612825197799	

Footnote: C - CRATE REEL PUT-UP.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.