

Illustration



Technical drawing of the 1000W power supply unit showing dimensions: width 50, height 125, and depth 84.



URL Webshop	https://shop.murrelektronik.com/85132
GTIN	4048879694469
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-7.1	27049002
ECLASS-8.0	27049002
ECLASS-8.1	27049002
ECLASS-9.0	27040701
ECLASS-9.1	27040701
ECLASS-10.0.1	27040701
ECLASS-10.1	27040701
ECLASS-11.0	27040701
ECLASS-11.1	27040701

ECLASS-12.0	27040701
ECLASS-13.0	27040701
ECLASS-14.0	27040701
ETIM-5.0	EC002540
ETIM-6.0	EC002540
ETIM-7.0	EC002540
ETIM-8.0	EC002540
customs tariff number	85044083
EAN	4048879694469
Packaging unit	1

Electrical data

Parallel connection	No
Series connection	Yes
Number of devices series connection max.	2

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage AC min.	100 V
Input voltage AC max.	240 V
Nominal input voltage AC	100 V
Nominal current AC	1.3 A @ 100 V , 0.6 A @ 240 V
Inrush current max.	20 A @ 230 V
Efficiency	84 % @ 115 V AC 85 % @ 230 V AC
Characteristic back-up fuse	Inertia
Fuse protection primary side internal	4 A

Electrical data | Output

Output voltage adjustable	Yes
Output voltage DC	24 V
Output voltage DC min.	23 V
Output voltage DC max.	28 V
Output current	2,5 A
Spikes (s-s) max.	50 mV
Ripple effective max.	10 mV

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Overload protection output	Yes
Short-circuit protection output	Yes

Mechanical data | Mounting data

Height	125 mm
Width	50 mm
Depth	84 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	40 °C
Derating from	40 °C
Ambient temperature (storage, transport)	-20 °C
Relative humidity (operation)	20 %
Additional condition relative humidity	no condensation

Conformity

Product standard	EN IEC 61010-2-201
------------------	--------------------

EMC	EN 61000-3-2
-----	--------------

Connection type 2

Family construction form	terminal
--------------------------	----------

No. of poles	3
--------------	---

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	PE
-------	----

PIN 2	N
-------	---

PIN 3	L
-------	---

Family construction form	terminal
--------------------------	----------

No. of poles	4
--------------	---

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	-
-------	---

PIN 2	-
-------	---

PIN 3	+
-------	---

PIN 4	+
-------	---