

EMPARRO POWER SUPPLY 1-PHASE,


IN: 100-240VAC OUT: 24-28VDC/20A

Art.No.: 85442
Weight: 1.256 kg
Country of origin: CZ
Model designation: Emparro 20-100-240/24

INPUT: 90...265 V AC/90...250 V DC
OUTPUT: 24...28 V DC
Current: 20 A

Link to Product

Illustration



Product may differ from Image



Header

Material short text Emparro 20-100-240/24

Commercial data

URL Webshop	https://shop.murrelektronik.com/85442
GTIN	4048879402910
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-7.1	27049002
ECLASS-8.0	27049002
ECLASS-8.1	27049002
ECLASS-9.0	27040701
ECLASS-9.1	27040701
ECLASS-10.0.1	27040701
ECLASS-10.1	27040701
ECLASS-11.0	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ECLASS-13.0	27040701

ECLASS-14.0	27040701
ETIM-5.0	EC002540
ETIM-6.0	EC002540
ETIM-7.0	EC002540
ETIM-8.0	EC002540
customs tariff number	85044095
EAN	4048879402910
Packaging unit	1

Electrical data

Security level	SELV
Parallel connection	Yes
Number of devices parallel connection max.	5
Series connection	Yes
Number of devices series connection max.	2

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage AC min.	90 V
Input voltage AC max.	265 V
Nominal input voltage AC	100 V
Input voltage DC min.	90 V
Input voltage DC max.	250 V
Nominal current AC	5.2 A @ 100 V , 2.2 A @ 240 V
Inrush current max.	23 A @ 230 V
Power factor	230 V AC
Efficiency	91.7 % @ 110 V AC 94.1 % @ 230 V AC
Characteristic back-up fuse	Inertia
Fuse protection primary side internal	10 A

Electrical data | Output

Output voltage adjustable	Yes
Output voltage DC	24 V
Output voltage DC min.	24 V
Output voltage DC max.	28 V
Output current	20 A
Mains failure bridging min.	30 ms @ 100 V AC
Power Boost	150 %
Duration Power Boost min.	4 s
Spikes (s-s) max.	200 mV
Ripple effective max.	50 mV

Installation | Connection

Connection	Push-In spring clamp terminals
------------	--------------------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Overload protection output	Yes
Short-circuit protection output	Yes

Mechanical data | Mounting data

Height	123 mm
Width	85 mm
Depth	138 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

The information in this Product-PDF has been compiled with the utmost care.
 Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-01-11

Operating temperature min.	-40 °C
Operating temperature max.	60 °C
Derating from	45 °C
Ambient temperature (storage, transport)	-40 °C
Relative humidity (operation)	5 %
Additional condition relative humidity	no condensation

Conformity

Product standard	EN IEC 61010-2-201
EMC	EN 55011 B, EN 61000-3-2
Low Voltage Directive	EN 61204-3

Approvals

SEMI F47	compliant
----------	-----------

Connection type 3

Connection type 1	Alarm
Connection type 2	Input
Connection type 3	Output
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	13
PIN 2	14
Family construction form	terminal
No. of poles	3
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	PE
PIN 2	N
PIN 3	L
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	-
PIN 2	-
PIN 3	+
PIN 4	+