

MST 1-PHASE CONTROL AND ISOLATION TRANSFORMER


P: 630VA IN: 208...550VAC OUT: 2x115VAC


Art.No.: 86149
Weight: 9.5
Country of origin: CZ
Model designation: MST 0630-208...550/2x115

Single-phase - Control and Isolation Transformers
630 VA
Isolation class T 40/B
Other voltages on request.

Link to Product

Illustration





Pri. und Sec. Anschluß: /
Pri. and Sec. connection

Eingang [V] / Input	Klemme: / Clamps	Brücke: / Bridge	I _N
208	1-2	1+4 / 3+7	3.3 A
230*	5-7	1+4 / 3+7	3.0 A
380	1-6	2+5	1.8 A
400	1-6	2+4	1.7 A
420	1-6	3+5	1.6 A
440	1-6	3+4	1.6 A
460	1-7	2+4	1.5 A
480	1-7	3+5	1.4 A
500	1-7	3+4	1.4 A
525	1-8	3+5	1.3 A
550	1-8	3+4	1.3 A
2x 115	9-11 u. 10-12	-	2.8 A
115	9-12	9+10/11+12	5.5 A
230*	9-12	10+11	2.8 A

*Auslieferungszustand / delivered

Product may differ from Image



Header	
Material short text	MST 0630-208...550/2x115
Commercial data	

URL Webshop	https://shop.murrelektronik.com/86149
GTIN	4048879449120
ECLASS-6.0	27031302
ECLASS-6.1	27031302
ECLASS-7.0	27031302
ECLASS-7.1	27031302
ECLASS-8.0	27031302
ECLASS-8.1	27031302
ECLASS-9.0	27031302
ECLASS-9.1	27031302
ECLASS-10.0.1	27031302
ECLASS-10.1	27031302
ECLASS-11.0	27031302
ECLASS-11.1	27031302
ECLASS-12.0	27031302
ECLASS-13.0	27031302
ECLASS-14.0	27031302
ETIM-5.0	EC002486
ETIM-6.0	EC002486
ETIM-7.0	EC002486
ETIM-8.0	EC002486
customs tariff number	85043180
EAN	4048879449120
Packaging unit	1

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage AC	230 V
Input voltage AC	420, 208, 525, 550, 230, 380, 400, 440, 460, 480, 500
Nominal input voltage AC	230 V
Nominal current AC	3 A @ 230 V , 1.5 A @ 400 V
Max. inrush current	12 A
Short-circuit current	15.6 A

Electrical data | Output

Output voltage adjustable	yes
Output voltage	1 × 230 / 1 × 115 / 2 × 115 V AC
Output voltage AC 1	230 V
Output voltage AC 2	115 V
Power rating AC max.	630 VA

Device protection | Electrical

Insulation test voltage input - output	4 kV
--	------

Mechanical data | Mounting data

Height	129.4 mm
Width	150 mm
Depth	150 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, Long-hole mounting, (EN 60715)
Mounting dimension a	107.5 mm
Mounting dimension b	122 mm
Diameter bore	4.8 mm
Length bore	8.4 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	40 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C

Conformity

Product standard	EN IEC 61558-1, EN IEC 61558-2-4, IEC 62041 category 0
------------------	--

Connection type 5

Connection type 1	Input
Connection type 2	Input
Connection type 3	Output
Connection type 4	Output
Family construction form	terminal
No. of poles	8
Gender	female
Connection	Screw terminals SK
PIN 1	1
PIN 2	2
PIN 3	3
PIN 4	4
PIN 5	5
PIN 6	6
PIN 7	7
PIN 8	8
Family construction form	terminal
No. of poles	8
Gender	female
Connection	Plug-in terminals RK
PIN 1	1
PIN 2	2
PIN 3	3
PIN 4	4
PIN 5	5
PIN 6	6
PIN 7	7
PIN 8	8
Family construction form	terminal
No. of poles	4
Gender	female
Connection	Screw terminals SK
PIN 1	9
PIN 2	10
PIN 3	11
PIN 4	12
Family construction form	terminal
No. of poles	4
Gender	female
Connection	Plug-in terminals RK
PIN 1	9
PIN 2	10
PIN 3	11
PIN 4	12
Family construction form	terminal
No. of poles	1

Gender	female
Color contact carrier	metallic
Connection	Screw terminals SK
PIN 1	PE