


Product: [8437](#)


Audio, Control and Instrumentation, 1 Pair 22 AWG Solid, Shielded, CMG

Product Description

1 Twisted Pair 22 AWG solid TC, PVC insulation, polyester tape, TC braid shield (90% coverage), 22 AWG solid TC drain wire, PVC jacket.

Technical Specifications
Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Construction Details
Conductor

Size	Stranding	Material	No. of Pairs
22	Solid	TC - Tinned Copper	1

Insulation

Material	Color Code
PVC - Polyvinyl Chloride	Black & Red

Outer Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	90%

Outer Jacket

Separator	Material	Nom. Diameter
Polyester Tape	PVC - Polyvinyl Chloride	0.188 in

Electrical Characteristics
Electricals

Nom. Characteristic Impedance
46 Ohm

Voltage

UL Voltage Rating
300 V RMS (UL AWM Style 2095)

Mechanical Characteristics
Temperature

UL Temperature	Operating
80°C (UL AWM Style 2095)	-20°C To +80°C
Max. Pull Tension:	48 lbs (22 kg)
Bulk Cable Weight:	22 lbs/1000ft (33 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	UL1685 FT4 Loading

NEC / UL Compliance:	CMG
AWM Compliance:	AWM 2095 (300 V 80°C)
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Overall Cabling Separator Material: Polyester Tape
--------	--

History

Update and Revision:	Revision Number: 0.350 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants					
Item #	Color	Putup Type	Length	UPC	Footnote
8437 0101000	Black	Reel	1,000 ft	612825207177	C
Footnote:	C - CRATE REEL PUT-UP.				

© 2026 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.