


Product: [8660](#)

Shielding & Bonding, TC Braid #14.3AWG

[Request Sample](#)
Product Description

Shielding & Bonding, TC Braid 14.3AWG (96x34)

Technical Specifications
Product Overview

Suitable Applications: for shielding and bonding cable

Construction Details
Conductor

Element	No. of Elements	Size	Stranding	Material
Braid	1	14.3	96x34	TC - Tinned Copper

Overall Cable Diameter (Nominal): 0.153 in (3.89 mm)

Electrical Characteristics
Electricals

Nom. Conductor DCR	Max. Current
2.72 Ohm/1000ft	Single conductor in free air @ 30°C: 27.0 A

Mechanical Characteristics
Bend Radius

Stationary Min.	Installation Min.
0.16 in (4.1 mm)	0.16 in (4.1 mm)

Max. Pull Tension: 52 lbs (24 kg)

Bulk Cable Weight: 12 lbs/1000ft

Standards and Compliance

Sustainability: CA Prop 65

European Directive Compliance: EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

Product Notes

Notes: AWG size is approximated.

History

Update and Revision: Revision Number: 0.445 Revision Date: 09-07-2025

Part Numbers
Variants

Item #	Color	Putup Type	Length	UPC
8660 00050	None	Reel	50 ft	612825213888
8660 000250	None	Reel	250 ft	612825213871

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.