

**IMPACT67 COMPACT MODULE, PLASTIC**




Ethernet/IP, 16 dig Out

Art.No.: 55088  
 Weight: 0.440 kg  
 Country of origin: DE  
 Model designation: IMPACT67 E DO 16/0,5A

Digital outputs  
 DO16 - 0.5 A  
 Ethernet 10/100 Mbit/s; M12, D-coded  
 7/8", 5-pole, 2x max. 9 A  
 M12, 5-pole, A-coded  
 Connection cables are in the online shop under "Connection Technology".  
 Housing fully potted.  
 mounting compatible with I/O modules of the MVK series

[Link to Product](#)

**Illustration**



Product may differ from Image



**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/55088">https://shop.murrelektronik.com/55088</a>
GTIN	4048879051927
Customs tariff number	85389099
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-7.1	27242604
ECLASS-8.0	27242604
ECLASS-8.1	27242604
ECLASS-9.0	27242604
ECLASS-9.1	27242604
ECLASS-10.0.1	27242604
ECLASS-10.1	27242604
ECLASS-11.0	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ECLASS-13.0	27242604
ECLASS-14.0	27242604
ETIM-5.0	EC001599
ETIM-6.0	EC001599
ETIM-7.0	EC001599
ETIM-8.0	EC001599
customs tariff number	85389099
EAN	4048879051927
Packaging unit	1
<b>Electrical data   Supply</b>	
Total current US max.	9 A
Total current UA max.	9 A
<b>Electrical data   Output</b>	
Output current per pin max.	0,5 A
Overload resistant	Yes
Short-circuit protected	Yes
<b>Industrial communication   Ethernet/IP</b>	
Addressing	Rotary switch, BOOTP, DHCP
<b>Diagnostics</b>	
Diagnostic	No voltage, Under voltage
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module and channel
LED display	Ethernet connection/data traffic
<b>Device protection   Electrical</b>	
Degree of protection (EN IEC 60529)	IP67
<b>Mechanical data   Mounting data</b>	
Height	39 mm
Width	63 mm
Depth	225 mm
Suitable for mounting type	2-hole screw mounting
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Ambient temperature (storage, transport)	-25 °C ... 70 °C
<b>Connection type 4</b>	

Connection type 1	0-7
Connection type 2	Port1, Port2
Connection type 3	Power In
Connection type 4	Power Out
Family construction form	M12
No. of poles	5
Coding	A
Gender	female
Color contact carrier	black
PIN 1	n.c.
PIN 2	DO 10-17
PIN 3	0 V
PIN 4	DO 00-07
PIN 5	PE
Family construction form	M12
No. of poles	4
Coding	D
Gender	female
Color contact carrier	black
Mounting method	inserted, screwed
Tightening torque	0,6 Nm
PIN 1	TD +
PIN 2	RD +
PIN 3	TD -
PIN 4	RD -
PIN 5	n.c.
Family construction form	7/8"
No. of poles	5
Gender	male
Color contact carrier	black
PIN 1	0 V
PIN 2	0 V
PIN 3	PE
PIN 4	24 V DC (US)
PIN 5	24 V DC (UA)
Family construction form	7/8"
No. of poles	5
Gender	female
Color contact carrier	black
PIN 1	0 V
PIN 2	0 V
PIN 3	PE
PIN 4	24 V DC (US)
PIN 5	24 V DC (UA)