


Product: [8772](#)

Electronic, 3 C #20 Str TC, PE Ins, OS, PVC Jkt, CM

[Request Sample](#)
Product Description

Electronic, 3 Conductor 20AWG (7x28) Tinned Copper, PE Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, CM

Technical Specifications
Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Construction Details
Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	20 AWG	7x28	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PE - Polyethylene	0.017 in (0.43 mm)	0.070 in (1.8 mm)	Black, Red, Clear

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	20 AWG (7x28) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.033 in (0.84 mm)	0.218 in (5.54 mm)

Overall Cable Diameter (Nominal): 0.218 in (5.54 mm)

Electrical Characteristics
Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	11.1 Ohm/1000ft	27 pF/ft (89 pF/m)	51 pF/ft (170 pF/m)	8 Amps per Conductor at 30°C
Nom Outer Shield DCR:		8.08 Ohm/1000ft (26.5 Ohm/km)		

Voltage

UL Voltage Rating
300 V (CM), 300 V (UL AWM 2093)

Mechanical Characteristics
Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

Bend Radius

Stationary Min.	Installation Min.
2.2 in (56 mm)	2.2 in (56 mm)

Max. Pull Tension:	50.4 lbs (22.9 kg)
Bulk Cable Weight:	28 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 UL loading , IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2093
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.537 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
8772.00152	Chrome	Reel	152 m	8719605019370	
8772.00U152	Chrome	UnReel	152 m	8719605019394	
8772.00305	Chrome	Reel	305 m	8719605019387	
8772.00U305	Chrome	UnReel	305 m	8719605019400	
8772.K0305	Chrome	Reel	305 m	8719605019417	
8772.K0U305	Chrome	Unreel	305 m	8719605019424	
8772 060500	Chrome	Reel	500 ft	612825215806	C
8772 060U500	Chrome	UnReel	500 ft	612825215783	
8772 0601000	Chrome	Reel	1,000 ft	612825215790	C
8772 060U1000	Chrome	UnReel	1,000 ft	612825215776	
8772 0605000	Chrome	Reel	5,000 ft	612825215813	

Footnote:

C - CRATE REEL PUT-UP.

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.