



## Product: [89907](#)

Thinnet 10BASE2, RG-58A/U Type, #20 Str, FFEP, Duobond II+TC Braid, PVDF Jkt, CMP

### Product Description

IEEE 802.3 Ethernet Thinnet 10BASE2, 20 AWG (19x32) tinned copper conductor, foam FEP insulation, Duobond® II (100% coverage) + tinned copper braid shield (95% coverage), fluorocopolymer jacket, CMP

### Technical Specifications

#### Product Overview

Suitable Applications:	Thin Ethernet (IEEE 802.3 10BASE2)
------------------------	------------------------------------

#### Construction Details

RG Type:	58
----------	----

##### Conductor

Size	Stranding	Nom. Diameter	Material
20 AWG	19x32	0.037 in	TC - Tinned Copper

##### Insulation

Material	Nom. Insulation Diameter	Color Code
PFA - Perfluoroalkoxy (Foam)	0.100 in (2.54 mm)	White

##### Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Tinned Copper (TC)		93%

##### Outer Jacket

Material	Nom. Diameter
PVDF - Polyvinylidene Fluoride	0.165 in (4.19 mm)

Overall Cable Diameter (Nominal): 0.165 in (4.19 mm)

### Electrical Characteristics

#### Attenuation

Frequency	Nom. Attenuation
1 MHz	0.43 dB/100ft
10 MHz	1.3 dB/100ft
50 MHz	2.91 dB/100ft
100 MHz	4.18 dB/100ft
200 MHz	6.1 dB/100ft
400 MHz	9.2 dB/100ft
700 MHz	12.9 dB/100ft
900 MHz	15.0 dB/100ft
1000 MHz	16.0 dB/100ft

#### Power Rating

Frequency	Max. Power Rating
1 MHz	6,450 W

10 MHz	1,850 W
50 MHz	890 W
100 MHz	640 W
200 MHz	470 W
400 MHz	360 W
700 MHz	290 W
900 MHz	270 W
1,000 MHz	260 W

#### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
8.5 Ohm/1000ft (28 Ohm/km)	5.8 Ohm/1000ft (19 Ohm/km)	26.0 pF/ft (85.3 pF/m)	50 Ohm	80%

#### Voltage

UL Voltage Rating
300 V (CMP)

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
150°C	-15°C to +150°C

##### Bend Radius

##### Installation Min.

1.6 in (41 mm)

Max. Pull Tension:	45 lbs (20 kg)
Bulk Cable Weight:	26 lbs/1000ft

#### Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Aerial - When supported by messenger wire
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262
CPR Compliance:	CPR Euroclass: Eca
CEC / C(UL) Compliance:	CMP
IEEE Compliance:	802.3 10Base2
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	9907

#### History

Update and Revision:	Revision Number: 0.524 Revision Date: 09-07-2025
----------------------	--

#### Part Numbers

##### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
89907 E4X500	Gray, Light Dec	Reel	500 ft	612825221449	C
89907 E4X1000	Gray, Light Dec	Reel	1,000 ft	612825221425	C
89907 E4X2500	Gray, Light Dec	Reel	2,500 ft	612825221432	C Z

Footnote: C - CRATE REEL PUT-UP., Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

© 2026 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

