

CUBE20S COUNTER MODULE

2X32Bit 400Khz 45 Parameter Bytes

Art.No.: 57162

Weight: 0.065 kg

Country of origin: TH

Model designation: Cube20S Counter mod. 2X32Bit 400Khz 45PB

Counter module

2× 32 Bit

max. 400 kHz


OUTPUT: 12 Byte

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

URL Webshop	https://shop.murrelektronik.com/57162
GTIN	4048879422956
EU-Customs tariff number	90291000
US-Customs tariff number	9029108000
ECLASS-6.0	27242605
ECLASS-6.1	27242605
ECLASS-7.0	27242605
ECLASS-7.1	27242605
ECLASS-8.0	27242605
ECLASS-8.1	27242605
ECLASS-9.0	27242605
ECLASS-9.1	27242605
ECLASS-10.0.1	27242605
ECLASS-10.1	27242605
ECLASS-11.0	27242605
ECLASS-11.1	27242605
ECLASS-12.0	27242605
ECLASS-13.0	27242605

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-08-20

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

ECLASS-14.0	27242605
ETIM-5.0	EC001601
ETIM-6.0	EC001601
ETIM-7.0	EC001601
ETIM-8.0	EC001601
ETIM-9.0	EC001601
ETIM-10.0	EC001601
customs tariff number	90291000
EAN	4048879422956
Packaging unit	1
Electrical data	
Number of counters	2
Counter width	32 bits
Counter frequency max.	400 kHz
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage DC min.	20,4 V
Operating voltage DC max.	28,8 V
Current consumption max.	75 mA
Diagnostics	
Short circuit diagnosis	Yes
Overload diagnosis	Yes
Diagnostic	Under voltage
Diagnostic via BUS	per module
Diagnostic via LED	per module
LED display	Ethernet connection/data traffic
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Height	109 mm
Width	12,9 mm
Depth	76,5 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-25 °C ... 70 °C
Connection type 2	
Connection type 1	Power
Connection type 2	Power
Family construction form	terminal
No. of poles	8
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.

PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys
Family construction form	terminal
No. of poles	8
Gender	female
Connection	Spring clamp terminals FK
PIN 1	A 0
PIN 2	24 V DC
PIN 3	0 V
PIN 4	A 1
PIN 5	B 0
PIN 6	24 V DC
PIN 7	0 V
PIN 8	B 1