

5 Port unmanaged Gigabit Switch 4 PoE Ports IP20 metal 48 V



Art.No.: 58190

Weight: 0.420 kg

Country of origin: TW

Model designation: TREE 5TX 4PoE GE 48V

5 Port Unmanaged IP20 PoE Gigabit Switch
 48 V power supply

[Link to Product](#)
Illustration


Product may differ from Image


Commercial data

URL Webshop	https://shop.murrelektronik.com/58190
GTIN	4048879843676
EU-Customs tariff number	85176200
ECLASS-6.1	19170106
ECLASS-7.0	19170106

ECLASS-7.1	19170106
ECLASS-8.0	19170106
ECLASS-8.1	19170106
ECLASS-9.0	19170106
ECLASS-9.1	19170106
ECLASS-10.0.1	19170402
ECLASS-10.1	19170402
ECLASS-11.0	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ECLASS-13.0	19170402
ECLASS-14.0	19170402
customs tariff number	85176200
EAN	4048879843676
Packaging unit	1

Electrical data | Supply

Operating voltage DC min.	12 V
Operating voltage DC max.	52 V
Power consumption max.	6 W
PoE voltage amplifier	Yes

Industrial Communication

Data transmission rate max.	1.000 Mbit/s
-----------------------------	--------------

Industrial communication | Ethernet functionality

VLAN unmanaged (IEEE 802.1Q)	No
Switch type	unmanaged
duplex	Full duplex
Auto-negotiation	Yes
Auto-crossover	Yes

Diagnostics

Alarm contact	Yes
Diagnostic	No voltage
LED display	Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Material data

housing	Metal
Color housing	black

Mechanical data | Mounting data

Height	110 mm
Width	89,6 mm
Depth	45,4 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	70 °C
Ambient temperature (storage, transport)	-40 °C ... 85 °C

Connection type 2

Connection type 1	5
Connection type 2	X1
Family construction form	RJ45

No. of poles	8
Gender	female
Color contact carrier	black
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.
Family construction form	terminal
No. of poles	7
Gender	male
Color contact carrier	green
Connection	Plug-in terminals RK
PIN 1	V 2 +
PIN 2	V 2 -
PIN 3	Relay (NO)
PIN 4	Relay (NO)
PIN 5	V 1 +
PIN 6	V 1 -
PIN 7	FE