

M8 male recept. A-cod. front

PUR-wires 3x0.25 0.5m

Art.No.: 7000-08552-9700050

Weight: 0.019 kg

Country of origin: DE




Model designation: MSHFV-R970_0.5


Flange male

M8, 3-pole


Front mounting

with multi-strand wire

[Link to Product](#)**Illustration**



Product may differ from Image



Cable length	0,50 m
Side 1	
Family construction form	M8
No. of poles	3
Coding	A
Gender	male
Mounting method	inserted, screwed
Threaded hole	M8 x 1
Tightening torque	0,4 Nm
Width across flats	SW10
Material	Brass
Material contact	Copper alloy
Coating contact	gold plated
Degree of protection (EN IEC 60529)	IP67
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-08552-9700050
GTIN	4048879435147
EU-Customs tariff number	85444290
US-Customs tariff number	8544429090
ECLASS-6.0	27279220
ECLASS-6.1	27279220
ECLASS-7.0	27440103
ECLASS-7.1	27440103
ECLASS-8.0	27440103
ECLASS-8.1	27440103
ECLASS-9.0	27440103
ECLASS-9.1	27440109
ECLASS-10.0.1	27440109
ECLASS-10.1	27440103
ECLASS-11.0	27440109
ECLASS-11.1	27440103
ECLASS-12.0	27440103
ECLASS-13.0	27440109

ECLASS-14.0	27440109
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
ETIM-9.0	EC001855
ETIM-10.0	EC001855
customs tariff number	85444290
EAN	4048879435147
Packaging unit	1

Electrical data

Conductor resistance (wire)	77.8 Ω /km @ 20 °C
-----------------------------	---------------------------

Electrical data | Supply

Operating voltage AC max.	50 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
Nominal voltage AC max.	300 V

Diagnostics

Status indication LED	No
-----------------------	----

Installation | Connection

Mounting set	M8 x 1
--------------	--------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Protection NEMA	6P, 4, 3
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. wire	4,5 A
Rated surge voltage	1,5 kV
Isolation resistance	20 M Ω x km
Withstand voltage (wire - wire)	1.5 kV @ 60 s
Material group (IEC 60664-1)	I

Mechanical data

Amount strands (wire)	14
Diameter of single wires	0,15 mm

Mechanical data | Material data

Screw connection	Brass
Coating of fitting	nickel plated
Material wire insulation	PUR
Ingredient freeness wire insulation	lead-free, CFC-free, halogen-free
Material conductor wire	copper stranded wire, tinned

Mechanical data | Mounting data

Mounting method	Schraubgewinde
Looking techniques	Schraubgewinde
Cable weighth	3,5 g/m

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Operating temperature min. (static)	-40 °C
Operating temperature max. (static)	-40 °C ... 90 °C

Operating temperature min. (dynamic)	-25 °C
Operating temperature max. (dynamic)	-25 °C ... 90 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Approvals

UL 50E	Yes
--------	-----

Resistances | Cable

Cable identification	970
Cable weight	0 g/m
Stranding	1 × 3 wires stranded
Wire arrangement	BN, BU, BK
Material wire insulation	PUR
Amount wires	3
Outer diameter insulation	1.1 mm ± 0.1 mm
Conductor crosssection (wire)	0,25 mm²
Material conductor wire	copper stranded wire, tinned
Core construction (wire)	14 × 0.15 mm
Ingredient freeness wire insulation	lead-free, CFC-free, halogen-free
Conductor resistance (wire)	77.8 Ω/km @ 20 °C
Nominal voltage max.	300 V
Withstand voltage (wire - wire)	1.5 kV @ 60 s
Current load capacity max. (wire)	4,5 A
Current load capacity (standard)	to DIN VDE 0298-4
Isolation resistance	20 MΩ × km
Operating temperature (static)	-40 °C ... 90 °C
Operating temperature (dynamic)	-25 °C ... 90 °C
Flame resistance	IEC 60332-1-2
Other resistances	resistant to hydrolysis, resistant to microbes
Notes	application-related testing