

M8 male recept. A-cod. front

PUR-wires 4x0.25 0.2m

Art.No.: 7000-08562-9690020

Weight: 0.013 kg

Country of origin: DE

Model designation: MSHFV-T969_0.2

Flange male

M8, 4-pole




Front mounting


with multi-strand wire

The resistance to aggressive media should be individually tested for your application. Further details on request.


Good chemical and oil resistance (oil resistance does not apply to use with PVC cable)

Further cable lengths on request.

[Link to Product](#)**Illustration**



Product may differ from Image



Toleranz Kabellängen:
cable lenght tolerances

0m < L ≤ 0,5m	+0,03m	1,0m < L ≤ 3,0m	+0,1m
0,5m < L ≤ 1,0m	+0,05m	3,0m < L	±1,5%



Cable length	0,20 m
Side 1	
Family construction form	M8
No. of poles	4
Coding	A
Gender	male
Mounting method	inserted, screwed
Threaded hole	M8 x 1
Tightening torque	0,4 Nm
Width across flats	SW10
Material	Brass
Material contact	Copper alloy
Coating contact	gold plated
Degree of protection (EN IEC 60529)	IP67
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-08562-9690020
GTIN	4048879434997
EU-Customs tariff number	85444290
US-Customs tariff number	8544429090
ECLASS-6.0	27279220
ECLASS-6.1	27279220
ECLASS-7.0	27440103
ECLASS-7.1	27440103
ECLASS-8.0	27440103
ECLASS-8.1	27440103
ECLASS-9.0	27440103
ECLASS-9.1	27440109
ECLASS-10.0.1	27440109
ECLASS-10.1	27440103
ECLASS-11.0	27440109
ECLASS-11.1	27440103
ECLASS-12.0	27440103
ECLASS-13.0	27440109

ECLASS-14.0	27440109
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444290
EAN	4048879434997
Packaging unit	1

Electrical data

Conductor resistance (wire)	77.8 Ω/km @ 20 °C
-----------------------------	-------------------

Electrical data | Supply

Operating voltage AC max.	50 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
Nominal voltage AC max.	300 V

Diagnostics

Status indication LED	No
-----------------------	----

Installation | Connection

Mounting set	M8 x 1
--------------	--------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Protection NEMA	6P, 4, 3
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. wire	4,5 A
Rated surge voltage	0,8 kV
Isolation resistance	20 MΩ × km
Withstand voltage (wire - wire)	1.5 kV @ 60 s
Material group (IEC 60664-1)	I

Mechanical data

Amount strands (wire)	14
Diameter of single wires	0,15 mm

Mechanical data | Material data

Screw connection	Brass
Coating of fitting	nickel plated
Material wire insulation	PUR
Ingredient freeness wire insulation	lead-free, CFC-free, halogen-free
Material conductor wire	copper stranded wire, tinned

Mechanical data | Mounting data

Mounting method	Schraubgewinde
Looking techniques	Schraubgewinde
Cable weight	3,5 g/m

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Operating temperature min. (static)	-40 °C
Operating temperature max. (static)	-40 °C ... 90 °C
Operating temperature min. (dynamic)	-25 °C
Operating temperature max. (dynamic)	-25 °C ... 90 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Conformity

Product standard	EN/IEC 61076-2-104 (M8)
------------------	-------------------------

Approvals

UL 50E	Yes
--------	-----

Resistances | Cable

Stranding	1 × 4 wires stranded
Wire arrangement	BN, BK, BU, WH
Material wire insulation	PUR
Amount wires	4
Outer diameter insulation	1.1 mm ± 0.1 mm
Conductor crossection (wire)	0,25 mm²
Material conductor wire	copper stranded wire, tinned
Core construction (wire)	14 × 0.15 mm
Ingredient freeness wire insulation	lead-free, CFC-free, halogen-free
Conductor resistance (wire)	77.8 Ω/km @ 20 °C
Nominal voltage max.	300 V
Withstand voltage (wire - wire)	1.5 kV @ 60 s
Current load capacity max. (wire)	4 A
Current load capacity (standard)	to DIN VDE 0298-4
Isolation resistance	20 MΩ × km
Operating temperature (static)	-40 °C ... 90 °C
Operating temperature (dynamic)	-25 °C ... 90 °C
Flame resistance	IEC 60332-1-2
Other resistances	resistant to hydrolysis, resistant to microbes
Notes	application-related testing