


Product: [9504](#)
RS-232, #24-4pr, SR-PVC, O/A Foil, PVC Jkt, CMG, 75Ω
Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, 4 twisted pairs, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications
Product Overview

Suitable Applications:	RS-232 Applications; Computer Communications; Low Voltage Analog Signals (4-20mA, 0-10V, ...); Low Voltage Digital Control (24V, ...); Line Level Audio; Panel Wiring
------------------------	---

Construction Details
Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	4	24 AWG	7x32	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.011 in (0.28 mm)	0.044 in (1.1 mm)	Black & Red, Black & White, Black & Green, Black & Blue

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.259 in (6.58 mm)

Overall Cable Diameter (Nominal): 0.259 in (6.58 mm)

Electrical Characteristics
Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Velocity of Prop.	Max. Current
Pair(s)	28.8 Ohm/1000ft	30 pF/ft (98 pF/m)	50 pF/ft (160 pF/m)	60%	2.2 Amps per Conductor at 25°C

Nom Outer Shield DCR: 16.19 Ohm/1000ft (53.12 Ohm/km)

Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

Mechanical Characteristics
Temperature

UL Temperature	Operating
80°C	-30°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
2.6 in (66 mm)	2.6 in (66 mm)

Max. Pull Tension:	50 lbs (23 kg)
Bulk Cable Weight:	32 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464, AWM I/II A
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	89504, 82504

History

Update and Revision:	Revision Number: 0.540 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
9504.0030	Chrome	Reel	30 m	8719605021144	
9504 060100	Chrome	Reel	100 ft	612825254263	
9504.00U152	Chrome	UnReel	152 m	8719605021151	
9504.01152	Chrome	Reel	152 m	8719605021175	
9504.00U305	Chrome	UnReel	305 m	8719605021168	
9504.01305	Chrome	Reel	305 m	8719605021182	
9504.K1305	Chrome	Reel	305 m	8719605021199	
9504 060500	Chrome	Reel	500 ft	612825254287	
9504 060U500	Chrome	UnReel	500 ft	612825254256	
9504 0601000	Chrome	Reel	1,000 ft	612825254270	C
9504 060U1000	Chrome	UnReel	1,000 ft	612825254249	
9504 0605000	Chrome	Reel	5,000 ft	612825254294	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.