



Product: [9578](#) 

Electronic, 4 C #18 Sol BC, PVC Ins, OS, Red PVC Jkt, FPLR

 [Request Sample](#)

Product Description

Electronic, 4 Conductor 18AWG (Solid) Bare Copper, PVC Insulation, Overall Beldfoil® Shield, Red PVC Outer Jacket, FPLR

Technical Specifications

Product Overview

Suitable Applications:	fire alarms; indoor applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...)
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	18 AWG	Solid	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.077 in (2.0 mm)	Black, Red, Yellow, Blue

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.037 in (0.94 mm)	0.263 in

Overall Cable Diameter (Nominal):	0.263 in
-----------------------------------	----------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Inductance	Max. Current
Conductor(s)	6.4 Ohm/1000ft	43 pF/ft (140 pF/m)	79.2 pF/ft (260 pF/m)	0.169 µH/ft (0.554 µH/m)	6.4 Amps per Conductor at 25°C
Nom Outer Shield DCR:		10.3 Ohm/1000ft (33.8 Ohm/km)			

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-40°C To +105°C

Bend Radius

Stationary Min.	Installation Min.
2.63 in (66.8 mm)	2.63 in

Max. Pull Tension:	87.5 lbs (39.7 kg)
Bulk Cable Weight:	48 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL1666 Riser, FT4
NEC / UL Compliance:	Article 760, Article 800, CMR, FPLR
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG, FAS105.
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	California State Fire Marshall

History

Update and Revision:	Revision Number: 0.402 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
9578 0021000	Red	612825256199	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.