

Product: [9585](#)


Audio, Control & Instrument, #24-25pr, PVC, PVC Jkt, CMG

Product Description

Audio, Control & Instrument Cable, 24 AWG solid tinned copper conductors, PVC insulation, twisted pairs, PVC jacket.

Technical Specifications
Product Overview

Suitable Applications:	telephone cables; low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); voice communications
------------------------	---

Construction Details
Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	25	24	Solid	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.01 in (0.25 mm)	0.041 in (1.0 mm)	White & Blue, White & Orange, White & Green, White & Brown, White & Gray, Red & Blue, Red & Orange, Red & Green, Red & Brown, Red & Gray, Black & Blue, Black & Orange, Black & Green, Black & Brown, Black & Gray, Yellow & Blue, Yellow & Orange, Yellow & Green, Yellow & Brown, Yellow & Gray, Purple & Blue, Purple & Orange, Purple & Green, Purple & Brown, Purple & Gray

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.04 in (1.0 mm)	0.48 in

Electrical Characteristics
Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
32.8 Ohm/1000ft	22 pF/ft (72 pF/m)	1 Amp per Conductor at 20°C

Voltage

UL Voltage Rating
300 V (CMG), 150 V (AWM 2576)

Mechanical Characteristics
Temperature

UL Temperature	Operating
80°C	-20°C To +80°C

Bend Radius

Stationary Min.	Installation Min.
4.8 in (120 mm)	4.8 in

Max. Pull Tension:	255 lbs (116 kg)
Bulk Cable Weight:	134 lbs/1000ft

Standards and Compliance

Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2576
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision: Revision Number: 0.325 Revision Date: 09-07-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9585 060500	Chrome	Reel	500 ft	612825256274	C
9585 0601000	Chrome	Reel	1,000 ft	612825256267	C

Footnote: C - CRATE REEL PUT-UP.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.