



REPRESENTATIVE IMAGE

Product: [9729NH](#) 

RS232/422 Low Cap, #24-2pr, FPO, Indiv. Foil, LSZH Jkt, 100Ω

Product Description

Computer EIA RS-232/422, Digital Audio Cable, 24 AWG stranded (7x32) tinned copper conductors, Datalene® insulation, 2 twisted pairs each individually Beldfoil® shielded (100% coverage), 24 AWG stranded tinned copper drain wire each pair, LSZH jacket.

Technical Specifications

Product Overview

Suitable Applications:	RS-422 applications; computer communications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); digital audio; panel wiring
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	2	24 AWG	7x32	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PE - Polyethylene (Foam)	0.019 in (0.48 mm)	0.061 in (1.5 mm)	Black & Red, Black & White

Inner Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.048 in (1.2 mm)	0.3 in (7.6 mm)

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Inductance	Nom. Velocity of Prop.	Max. Current
78.7 Ohm/km (24.0 Ohm/1000ft)	3.23 Ohm/1000ft (10.6 Ohm/km)	41 pF/m (12 pF/ft)	76.1 pF/m (23.2 pF/ft)	100 Ohm	0.23 µH/ft (0.75 µH/m)	76%	1 Amps per Conductor at 25°C

High Frequency (Nominal/Typical)

Frequency	Nom. Insertion Loss (Attenuation)
0.384 MHz	4.63 dB/100m
0.7056 MHz	5.35 dB/100m
0.768 MHz	5.91 dB/100m
1.024 MHz	6.5 dB/100m
1.4112 MHz	6.89 dB/100m
1.536 MHz	9.15 dB/100m
2.048 MHz	9.51 dB/100m
2.8224 MHz	13.16 dB/100m
3.072 MHz	1.35 dB/100m
4.096 MHz	1.57 dB/100m
5.6448 MHz	1.78 dB/100m

6.144 MHz	1.84 dB/100m
8.192 MHz	2.13 dB/100m
11.2896 MHz	2.45 dB/100ft
12.288 MHz	2.57 dB/100ft
24.576 MHz	3.57 dB/100ft

Voltage

Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-45°C To +80°C	-15°C To +80°C	-45°C To +80°C

Bend Radius

Installation Min.
79 mm (3.1 in)

Max. Pull Tension:	11 lbs (5.0 kg)
Bulk Cable Weight:	33 lbs/1000ft (49 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor - Euroclass Dca, Indoor, Outdoor, Non-Halogenated, Sunlight Resistance - UL 1581 sec 1200 Black Only, Oil Resistance - IRM 902 70°Cx4h, Oil Resistance - IEC 60811-404
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-24
CPR Compliance:	CPR Euroclass: Dca-s1,d1,a1; CPR UKCA Class: Dca-s1,d1,a1
CEC / C(UL) Compliance:	.
CENELEC Compliance:	EN 50290-2-20
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3, IEC 61034-2 - Smoke Density Min. Transmittance = 60%
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

Product Notes

Notes:	Datalene« insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.
--------	--

History

Update and Revision:	Revision Number: 0.452 Revision Date: 07-23-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
9729NH.00100	Chrome	Reel	100 m	8719605197238
9729NH.00152	Chrome	Reel	152 m	8719605022547
9729NH.00305	Chrome	Reel	305 m	8719605022554
9729NH.00500	Chrome	Reel	500 m	8719605022561
9729NH.001000	Chrome	Reel	1,000 m	8719605022530

© 2026 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.