


Product: [9732](#)
RS232/422 Low Cap, #24-9pr, FPE, Indiv. Foil, PVC Jkt, CM, 100Ω
Product Description

Computer EIA RS-232/422, Digital Audio Cable, 9-Pair, 24 AWG stranded (7x32) tinned copper conductors, Datalene® insulation, individually shielded with Beldfoil® (100% coverage), 24 AWG stranded tinned copper drain wire, overall PVC jacket.

Technical Specifications
Product Overview

Suitable Applications: RS-422 applications; computer communications; low voltage analog signals (4-20mA, 0-10V, ...); low voltage digital control (24V, ...); digital audio; panel wiring

Construction Details
Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	9	24 AWG	7x32	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PE - Polyethylene (Foam)	0.019 in (0.48 mm)	0.061 in (1.5 mm)	Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown, Black & Orange, Red & White, Red & Green

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC	each pair

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.048 in (1.2 mm)	0.488 in (12.4 mm)

Overall Cable Diameter (Nominal): 0.488 in (12.4 mm)

Electrical Characteristics
Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Inductance	Nom. Velocity of Prop.	Max. Current
Pair(s)	24 Ohm/1000ft (79 Ohm/km)	12.5 pF/ft (41.0 pF/m)	23.2 pF/ft (76.1 pF/m)	100 Ohm	0.23 μH/ft (0.75 μH/m)	76%	1.9 Amps per Conductor at 25°C

High Frequency (Nominal/Typical)

Frequency	Nom. Insertion Loss (Attenuation) [dB/100ft]
0.384 MHz	0.74
0.7056 MHz	0.87
0.768 MHz	0.88
1.024 MHz	0.94
1.4112 MHz	1.01
1.536 MHz	1.03
2.048 MHz	1.13
2.8224 MHz	1.29

3.072 MHz	1.35
4.096 MHz	1.57
5.6448 MHz	1.78
6.144 MHz	1.84
8.192 MHz	2.13
11.2896 MHz	2.45
12.288 MHz	2.57
24.576 MHz	3.57

Voltage

UL Voltage Rating
300 V (CM), 300 V (UL AWM 2493)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C (UL AWM 2493)	-20°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
4.9 in (120 mm)	4.9 in (120 mm)

Max. Pull Tension: 150 lbs (68 kg)

Bulk Cable Weight: 99 lbs/1000ft (150 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL1685 UL Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2493
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	89732

Product Notes

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

History

Update and Revision: Revision Number: 0.347 Revision Date: 09-07-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9732 060100	Chrome	Reel	100 ft	612825257776	
9732 060500	Chrome	Reel	500 ft	612825257790	C
9732 0601000	Chrome	Reel	1,000 ft	612825257783	C

Footnote: C - CRATE REEL PUT-UP.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.