


**Product: [9841](#)**
**RS485, 1 Pr #24 Str TC, PE Ins, OS+TC Brd, PVC Jkt, CM**
[Request Sample](#)
**Product Description**

RS-485, 1 Pair 24AWG (7x32) Tinned Copper, PE Insulation, Overall Beldfoil®+Tinned Copper Braid(90%) Shield, PVC Outer Jacket, CM

**Technical Specifications**
**Product Overview**

Suitable Applications: RS-485, POS; Computer communications; Low Voltage Analog Signals (4-20ma, 0-10v, ...); Low Voltage Digital Control (24v, ...); Line Level Audio; Panel Wiring; serial communication (RS-485 standard) comprising of PLCs, VFDs, HMI, motors, RTU, SCADA, etc. within noisy environments over long distance, etc.

**Construction Details**
**Conductor**

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	24 AWG	7x32	TC - Tinned Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PE - Polyethylene	0.023 in (0.58 mm)	0.068 in (1.7 mm)	White/Blue Stripe & Blue/White Stripe

**Outer Shield**

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC
Braid	Tinned Copper (TC)	90%	

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.232 in (5.89 mm)

Outer Jacket1 Table Notes: Jacket OD +/- 0.020

Overall Cable Diameter (Nominal): 0.232 in (5.89 mm)

**Electrical Characteristics**
**Electricals**

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Delay	Nom. Velocity of Prop.	Max. Current
Pair(s)	24 Ohm/1000ft	12.8 pF/ft (42.0 pF/m)	23 pF/ft (75 pF/m)	120 Ohm	1.6 ns/ft	66%	2.1 Amps per Conductor at 25°C (10°C Temperature Rise)

Nom Outer Shield DCR: 3.4 Ohm/1000ft (11 Ohm/km)

**High Frequency (Nominal/Typical)**

Element	Frequency [MHz]	Nom. Insertion Loss (Attenuation)
Pair(s)	1	0.6 dB/100ft

**Voltage**

UL Voltage Rating
300 V (CM), 30 V (UL AWM 2919)

## Mechanical Characteristics

### Temperature

UL Temperature	Operating
80°C	-30°C to +80°C

### Bend Radius

Stationary Min.	Installation Min.
2.5 in (64 mm)	2.5 in (64 mm)

Max. Pull Tension: 72.3 lbs (32.8 kg)

Bulk Cable Weight: 36 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 UL Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2919
CEC / (UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	DMX-512
Plenum Number:	82841, 89841
Non-Plenum Number:	9841ZH

## History

Update and Revision: Revision Number: 0.690 Revision Date: 09-07-2025

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
9841.0030	Chrome	Reel	30 m	8719605022745	
9841 060100	Chrome	Reel	100 ft	612825259442	
9841.019999	Chrome	Reel	151 m	8719605022806	
9841.01152	Chrome	Reel	152 m	8719605022769	
9841.01305	Chrome	Reel	305 m	8719605022790	
9841.K1305	Chrome	Reel	305 m	8719605022844	
9841 060500	Chrome	Reel	500 ft	612825259473	C
9841 0601000	Chrome	Reel	1,000 ft	612825259459	C
9841.011000	Chrome	Reel	1,000 m	8719605022752	
9841.011525	Chrome	Reel	1,525 m	8719605022776	
9841.012000	Chrome	Reel	2,000 m	8719605022783	
9841 0605000	Chrome	Reel	5,000 ft	612825259480	
9841 06010000	Chrome	Reel	10,000 ft	612825259466	C
9841.03305	Violet	Reel	305 m	8719605022837	
9841.031000	Violet	Reel	1,000 m	8719605022820	
9841.02305	Yellow	Reel	305 m	8719605022813	

Footnote: C - CRATE REEL PUT-UP.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.