

Product: [9908](#)

Lead Wire, #8 Str TC, PVC Ins, AWM 1028 AWM 1015
[Request Sample](#)
Product Description

Low Temp Plastic Lead Wire, 8AWG (84x27) Tinned Copper, PVC Insulation, AWM 1028 AWM 1015 CSA TYPE TEW 600V 105C

Technical Specifications
Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, internal wiring of appliances, machine tool wire
------------------------	--

Construction Details
Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	8 AWG	84x27	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	0.0475 in (1.21 mm)	0.25 in (6.4 mm)

Overall Cable Diameter (Nominal): 0.25 in (6.4 mm)

Electrical Characteristics
Electricals

Nom. Conductor DCR	Max. Current
6.5 Ohm/1000ft	Single conductor in free air @ 30°C: 6.5 A

Voltage

UL Voltage Rating
600 V RMS

Mechanical Characteristics
Temperature

UL Temperature	Operating
105°C	-30°C To +105°C

Bend Radius

Stationary Min.	Installation Min.
2.5 in (64 mm)	2.5 in (64 mm)

Max. Pull Tension: 45 lbs (20 kg)

Bulk Cable Weight: 17 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	VW-1
NEC / UL Compliance:	Article 310, MTW

AWM Compliance:	AWM 1015, AWM 1283, CSA AWM I A/B
CEC / C(UL) Compliance:	TEW
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.474 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
9908 010100	Black	Reel	100 ft	612825260646
9908 010250	Black	Reel	250 ft	612825260653
9908 002100	Red	Reel	100 ft	612825260592
9908 002250	Red	Reel	250 ft	612825260608
9908 009100	White	Reel	100 ft	612825260622
9908 009250	White	Reel	250 ft	612825260639

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.