

DESINA HYBRIDFELDBUS

PUR 2x0.34 + 4x1,5 violet 5m

Art.No.: 7000-33011-9640500

Weight: 0.847 kg

Country of origin: DE

Model designation: DESINA HYBRIDFELDBUS CU, 5m

Advantages of our connectors:

Our connectors are versatile and specially optimised for industrial environments. All connectors are 100% tested during the manufacturing process to ensure the highest quality and reliability.

The contacts are gold-plated, which ensures optimum conductivity. Thanks to the high degree of protection, the connectors are ideal for demanding industrial environments. They are also vibration-resistant - this is ensured by the union nut with vibration protection.

Our connectors are resistant to oils and cooling lubricants, but resistance to aggressive media should be tested for each specific application. Different cable lengths available [on request](#)

If you are missing technical information? Please feel free to use our [dictionary](#) to find more technical details.

Product details:

DESINA® ECOFAST®

Male straight – female straight

6-pole, CU

Shielded

Further cable lengths on request.


Han-Brid ® a registered trademark of HARTING KGaA.


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.


Link to Product

Illustration





Product may differ from Image



Cable length 5,00 m

Side 1

Family construction form	DESINA® ECOFAST®
Mounting method	inserted
Material	PC
Degree of protection (EN IEC 60529)	IP65

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-33011-9640500
EU-Customs tariff number	85444290
customs tariff number	85444290
EAN	4048879186797
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	24 V
Operating voltage DC max.	24 V
Current operating per contact max.	10 A

Device protection | Electrical

Additional condition protection degree	inserted, screwed
--	-------------------

Mechanical data | Material data

Screw connection	PC
------------------	----

Mechanical data | Mounting data

Looking techniques	Clip locking
--------------------	--------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Installation | Cable

Wire arrangement	(BK 1, BK 2, BK 3, BK 4), (RD, GN)
Material wire insulation	PVC
Amount wires	4
Conductor crossection (wire)	1,5 mm ²

Material wire insulation (type 2)	PVC
Amount wires (type 2)	2
Conductor crosssection (wire type 2)	0,34 mm ²
Material jacket	PUR
Outer-diameter (jacket)	10 mm ± 5 %
Jacket Color	violet / RAL 4001
Material inner jacket	PVC
Operating temperature (static)	-30 °C ... 70 °C
Operating temperature (dynamic)	-40 °C ... 60 °C
Bending radius (dynamic)	8 × Outer diameter