



Product: [9939](#) 

RS232, #22-3c, SR-PVC, O/A Foil+Braid, PVC Jkt, CMG

Product Description

Computer EIA RS-232 Cable, 22 AWG stranded (7x30) tinned copper conductors, semi-rigid PVC insulation, overall Beldfoil® (100% coverage) + tinned copper braid shield (65% coverage), PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	RS-232 Applications; Computer Communications; Low Voltage Analog Signals (4-20mA, 0-10V, ...); Low Voltage Digital Control (24V, ...); Line Level Audio; Panel Wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.011 in (0.28 mm)	0.050 in (1.3 mm)	Black, White, Red

Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	65%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.202 in (5.13 mm)

Overall Cable Diameter (Nominal): 0.202 in (5.13 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	14.7 Ohm/1000ft	37 pF/ft (120 pF/m)	67 pF/ft (220 pF/m)	2.8 Amps per Conductor at 25°C

Nom Outer Shield DCR: 6.2 Ohm/1000ft (20 Ohm/km)

Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C (UL CMG);80°C (UL AWM 2464)	-30°C to +80°C

Bend Radius

Stationary Min.	Installation Min.

2.4 in (61 mm)	2.4 in (61 mm)
----------------	----------------

Max. Pull Tension:	45 lbs (20 kg)
--------------------	----------------

Bulk Cable Weight:	24 lbs/1000ft
--------------------	---------------

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
----------------------------	--------------------------------------

Sustainability:	CA Prop 65
-----------------	------------

Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEC 60332-1-2
----------------------------------	---

CPR Compliance:	CPR Euroclass: Eca
-----------------	--------------------

NEC / UL Compliance:	Article 800, CMG
----------------------	------------------

AWM Compliance:	AWM 2464
-----------------	----------

CEC / C(UL) Compliance:	CMG
-------------------------	-----

European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
--------------------------------	--

UK Regulation Compliance:	UKCA Mark
---------------------------	-----------

APAC Compliance:	China RoHS II (GB/T 26572-2011)
------------------	---------------------------------

History

Update and Revision:	Revision Number: 0.499 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC
9939 060100	Chrome	612825264637
9939 0601000	Chrome	612825264644
9939 060500	Chrome	612825264651
9939 0605000	Chrome	612825264668

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.