



Product: [DAUP](#) 

Category 6A Cable, 4 Pair, U/UTP, CMP

Product Description

Category 6A Premise Horizontal Cable, 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, Flamarrest® PVC-LS Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet 10GBASE-T
------------------------	--

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
23 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
FEP - Fluorinated Ethylene Propylene	White & Blue, White & Orange, White & Green, White & Brown

Outer Jacket

Separator	Material	Material Trade Name	Nom. Diameter	Ripcord
Center Member (Patented X-Spline®), EquiBlock™ Barrier Technology	PVC - Polyvinyl Chloride	Flamarrest®	0.250 in (6.35 mm)	Yes

Overall Cable Diameter (Nominal):	0.250 in (6.35 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
82 Ohm/km (25 Ohm/1000ft)	45 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	45 ns/100m	69%

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Storage
75°C	-20°C To +75°C	-20°C To +75°C

Bend Radius

Stationary Min.
1 in (25 mm)

Max. Pull Tension:	25 lbs (11 kg)
--------------------	----------------

Bulk Cable Weight:	34 lbs/1000ft (51 kg/km)
--------------------	--------------------------

Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6
NEC / UL Compliance:	Article 800
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-116-732
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6A
Third Party Performance Verification:	Channel/Category 6A
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	DAUR

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

History

Update and Revision:	Revision Number: 0.127 Revision Date: 02-20-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
DAUP 0101000	Black	Reel	1,000 ft	
DAUP D151000	Blue	Reel	1,000 ft	
DAUP D15A1000	Blue	Reel in Box	1,000 ft	612825503941
DAUP 0081000	Gray	Reel	1,000 ft	
DAUP 005A1000	Green	Reel in Box	1,000 ft	612825503989
DAUP 0051000	Green, Dark	Reel	1,000 ft	
DAUP 0031000	Orange	Reel	1,000 ft	
DAUP 003A1000	Orange	Reel in Box	1,000 ft	612825503965
DAUP 0021000	Red	Reel	1,000 ft	
DAUP 0091000	White	Reel	1,000 ft	
DAUP 0041000	Yellow	Reel	1,000 ft	

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.