



Product: [FSSH048NG](#) 

Heavy Duty Loose Tube OS2 48F OSP Unitized Gel

Product Description

FX Outdoor Heavy Duty Loose Tube OS2 48 Fibers OSP Sub-Units(12F) Gel Black

Technical Specifications

Product Overview

Suitable Applications:	Outdoor
------------------------	---------

Fiber Specifications

Fiber Type:	OS2
Fiber Core Diameter:	8.2/125µm
Fiber Buffer Material:	Loose tube - Gel-filled
Fiber Count:	48
Fiber Color Coding:	TIA-598-D

Cable Construction

Number of Active Subunits:	4
Fibers Per Subunit:	12
Subunit Waterblocking:	Gel Filled
Subunit Diameter:	0.110 in (2.8 mm)
Central Strength Member Type:	Upjacketed GRP
Cable Core Water Blocking:	Waterblock Tape

Inner Jacket Specifications

Material:	PE - Polyethylene
-----------	-------------------

Outer Jacket Specifications

Jacket Material:	Thermoplastic
Nom. Diameter:	.54 (13.7)
Outer Jacket Color:	Black
Outer Jacket Ripcord:	2

Optical Characteristics

Wavelength	1310 nm	1550 nm
Max. Attenuation	0.40 dB/km	0.30 dB/km

Mechanical Characteristics

Minimum Bend Radius During Installation:	20x Cable OD
Minimum Bend Radius During Operation:	15x Cable OD
Max. Tensile Strength During Installation:	600 lbf (2700 N)
Max. Tensile Strength During Operation:	180 lbf (800 N)
Crush Resistance:	220
Bulk Cable Weight:	121 lbs/1000ft (180 kg/km)

Temperature Range

Installation Temperature Range:	-30C to +70C
Operating Temperature Range:	-40C to +70C
Storage Temperature Range:	-40C to +75C

Standards and Compliance

Environmental Suitability:	Outdoor
TIA/EIA Compliance:	ANSI/ICEA S-87-640

History

Update and Revision:	Revision Number: 0.89 Revision Date: 09-07-2025
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	UPC
FSSH048NG	Black	Reel	612825372714

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.